

BPF-1240, 40" X 12 GAUGE BOX & PAN BRAKE WITH FOOT CLAMP

752125

Precision and durability with innovative ergonomic features ensures ongoing accuracy and operation, without user fatigue.



FEATURES

- Wide Assortment of Finger widths allow greater versatility in the shop
- Black Ceramic Coated Fingers prevent rust and ensure longer finger life
- All body sections are welded steel plate with heavy truss rods and braces designed to give greater strength and durability
- Stop rod for repeatable bending
- Material clamping is foot operated to save strain on back and arms
- Air spring to assist in raising the clamping handle



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

BPF-1240, 40" X 12 GAUGE BOX & PAN BRAKE WITH FOOT CLAMP

752125

SPECIFICATIONS

Style (Type)	Floor Box and Pan
Mild Steel Capacity (Gauge)	12
Bending Length Capacity (In.)	40
Maximum Box Depth (In.)	2-1/2
Maximum Lift of Beam (In.)	1-7/8
Number and Width of Fingers (In.)	1 ea 1, 1-1/8, 1-3/8, 1-1/2, 1-3/4, 2, 3, 4, 6, 7-3/4, 10-5/8
Finger Nose Angle (Deg.)	42
Nose Radius (In.)	1/32
Overall Dimensions (L x W x H) (In.)	58 x 25 x 50
Weight (Lbs.)	705



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE