

SBR-40M, 40" 3 IN 1 SHEAR, BRAKE AND ROLL

756041

JET innovation allows machine shop professionals the ability to perform several vital tasks with a single compact machine. The Combination Shear, Brake and Roll handles the jobs of three separate machines, adding tremendous versatility to your metal forming operation, without crowding the shop floor. This high-quality triple threat is backed by the JET industry leading Two Year Warranty



FEATURES

- Combination shear, brake and roll in one compact machine (Shown with optional stand)
- Right or left hand operation
- Shear can be used for mild steel, aluminum, brass, copper, lead, plastic and zinc
- Brake is equipped with easily removable fingers that permit angle, channel, box and other complex bending operations
- Slip rolls are precision turned and ground with wire grooves
- Spring-loaded work hold down
- Back gauge
- Dual edge shear blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

SBR-40M, 40" 3 IN 1 SHEAR, BRAKE AND ROLL

756041



SPECIFICATIONS

Style (Type)	Combination
Mild Steel Capacity (Gauge)	20
Shearing Capacity (Gauge)	20
Bending Capacity (Gauge)	20
Rolling Capacity (Gauge)	20
Size of Slip Roll (L x Dia.) (In.)	40 x 1-5/8
Width of Upper Dies (In.)	1, 2, 2, 4, 6, 7,8, 12
Upper Die Height (In.)	4-3/4
Minimum Forming Radius (In.)	1
Wire Grooves (In.)	1/8, 3/16, 1/4
Base Dimensions (L x W x H) (In.)	16-1/2 x 43
Overall Dimensions (L x W x H) (In.)	56 x 23 x 30
Weight (Lbs.)	575

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE