

PH-24T, 24" PLANISHING HAMMER

756121

JET's 24" Planishing Hammer has a quick change set up on the upper dies and a deep throat that works to the middle of most panels. The head with 3-speed regulator is capable of 4,400 – 4,800 / 3,200 – 3,500 / 1,800 – 2,000 blows-per minute (BPM). Easy to-reach, adjustable flow control valve allows the user to deliver the proper BPM needed for any job. Operates on standard shop air.



FEATURES

- Smooths beads and forms mild steel sheet metal up to 16 Gauge
- Smooths beads and forms aluminum and copper up to 1/8 in. thick
- Machine supplied with a pair of upper and anvil dies
- 3-Position airflow regulates speeds of pneumatic hammer
- Machine controlled with 110V AC foot control
- 2-Die Set Brackets
- Quick change of upper dies
- Retractable handle makes machine easy to move around the shop
- Wider base support to prevent movement of machine while in use



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

PH-24T, 24" PLANISHING HAMMER

756121

SPECIFICATIONS

Frame Tube Sizes (In.)	4 x 4
Throat (In.)	24
Head Opening (In.)	2-1/2
Maximum Pressure (PSI)	90
Air Consumption (CFM)	8.8
3-Speed Regulator (Hits Per Min.)	4,400 - 4,800 / 3,200 - 3,500 / 1,800 - 2,000
Noise Level (DB)	93 - 105
Overall Dimensions (L x W x H) (In.)	61 x 31 x 28
Weight (Lbs.)	258



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE