Digital Rotator

The Serology Rotator is designed to give years of dependable service, even in the busiest laboratory. It's the ideal space-saving instrument for procedures that require constant or timed rotation (mixing) such as RPR, VDRL, latex tests and for procedures that require a nonstandard speed.

FEATURES

Widely used in VDRL, RPR, and EIA tests Stable and quiet operation Clear humidity tray Variable speed, timer control, and continuous operation

SPECIFICATIONS

Speed: 20-240rpm

Timer: 99 hours and 99 minute digital timer

Power supply: AC 110V 60Hz (220V 50/60Hz available) Load capacity: 4.4lbs at 20-150rpm 2.2lbs at 151-240rpm

WEIGHT AND DIMS

Platform: 9 x 9in (230 x 230mm)

Orbit diameter: 0.8in Weight: 8.6 lbs (3.9kgs)

Width: 10in Depth: 12in Height: 5.5in



Digital Rotator

Model #

Description

RTL-BLVD-24T1

110v Digital Rotator

RTL-BLVD-24T2

220v Digital Rotator



P 770.270.1394 F 770.270.2389

865 Marathon Parkway Lawrenceville GA 30046

SLS-7.5.3-L-054 | Rev 0 LWScientific.com