

PS-1652T, 52" X 16 GAUGE PNEUMATIC SHEAR

756203

The JET PS-1652T delivers the strength and accuracy your shop demands in a rugged, cast-iron grade frame. Capable of making the big cuts, and versatile enough to handle just about any job you need completed. The pneumatic control system ensures smooth operation and smooth cuts along the precision-aligned bed and beam.



FEATURES

- Hi-quality cast-iron grade frame to eliminate deflection across the blade-span and blade frame work
- Low cutting angle to cut narrow strips without twisting
- Precise bed and beam alignment assures working accuracy
- Adjustable working bed for correct setup according to the blade clearance
- 16 gauge maximum capacity for mild-steel
- 14 gauge maximum capacity for aluminum and copper alloys
- 40 Strokes per Minute - Full Length
- 8.8 Air Consumption - CFM



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

PS-1652T, 52" X 16 GAUGE PNEUMATIC SHEAR

756203

SPECIFICATIONS

Style (Type)	Pneumatic
Max. Soft. Alloy Capacity (Gauge)	12 - 14
Mild Steel Capacity (Gauge)	16
Shearing Length Capacity (In.)	52
Back Gauge Capacity (In.)	28-1/2
Front Gauge Capacity (In.)	28
Strokes Per Minute (Full Length)	40
Air Consumption (CFM)	25.3
Overall Dimensions (L x W x H) (In.)	60 x 24 x 43
Weight (Lbs.)	1,048



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE