


Pyrolon® CRFR

Heat Sealed Seams



Liquid Splash/ Chemical Barrier



Flame Resistant



Disposable, Chemical Resistant, and Flame Resistant, all rolled into one garment

Pyrolon® CRFR protective wear...They're unique. They're disposable. They're chemical resistant. And they're flame resistant, meeting NFPA 2113 requirements. Imagine, all these qualities in one protective garment. Only from Lakeland.

Pyrolon® CRFR garments bar contaminating flammables like paint, oil and grease, hazardous liquids and contaminants, and dry particulates from penetrating to inner clothing.

Pyrolon® CRFR features:

- Light chemical splash protection
- Self extinguishing
- Won't melt or drip
- Meets the NFPA 2113 requirements for section 5.1.9.
- Designed to be worn over primary FR protective clothing, for environments where flash fire is a concern.

Pyrolon® CRFR Physical Properties, 2.5 Mil

Physical Property	Test Method	Units	Test Results
Basis Weight		oz./sq. yd	4.92
Grab Tensile MD		lbs.	34
Grab Tensile XD		lbs.	27
Mullen Burst		lbs./sq.in.	35
Char Length MD		inches	4.7
Char Length XD		inches	4.5
Afterflame		seconds	<2
Thermal Protective Performance (TPP)		cal./cm2	6.8
Charge Decay	NFPA 99		Pass
Surface Resistance	EN1149-1:2006		Pass

Pyrolon® CRFR Penetration Data, 2.5 Mil, ASTM F903

Challenge Chemical	CAS Number	Physical State	Penetration Result
Acetone	67-64-1	Liquid	>60
Acetonitrile	75-05-8	Liquid	>60
Benzene	71-43-2	Liquid	>60
Carbon Disulfide	75-15-0	Liquid	>60
Diesel Fuel	N/A	Liquid	>60
Diethylamine	109-89-7	Liquid	>60
Crude Oil	N/A	Liquid	>60
Ethyl Acetate	141-78-6	Liquid	>60
n-Hexane	110-54-3	Liquid	>60
Hexamethylene Diisocyanate	822-06-0	Liquid	>60
Hydrochloric Acid	7647-01-0	Liquid	>60
Methanol	67-56-1	Liquid	>60
Methyl Ethyl Ketone (MEK)	78-93-3	Liquid	>60
Methyl Isobutyl Ketone	108-10-1	Liquid	>60
Monochlorobenzene	108-90-7	Liquid	>60
n-Butyl Acetate	123-86-4	Liquid	>60
Orthodichlorobenzene, Grade F	95-50-1	Liquid	>60
Polychlorinated Biphenyl (PCB)	92-52-4	Liquid	>60
Sodium Hydroxide, 50%	1310-73-2	Liquid	>60
Sulfuric Acid, 98%	7664-93-9	Liquid	45
Surrogate Gasoline (Toulene 50%) (Isooctane 50%)	108-88-3 540-84-1	Liquid	>60
Tetrachloroethylene	127-18-4	Liquid	>60
Toluene	108-88-3	Liquid	>60
Trichlorobenzene Mixture	Mixture	Liquid	>60
Xylene	1330-20-7	Liquid	>60

Note: Chemical Resistance Data is in accordance with ASTM F903 test method. Testing is performed on fabric samples only, not finished garments. Sources for all test data are independent laboratories. All tests were performed under laboratory conditions and not actual use conditions.



- Coverall 51100**
- Collar
 - Storm flap over zipper
 - Open wrists
 - Open ankles
 - Hemmed cuff
 - Sizes:** S - 5XL
 - Case Pack:** 6



- Coverall 51110**
- Collar
 - Storm flap over zipper
 - Elastic wrists
 - Elastic ankles
 - Sizes:** S - 5XL
 - Case Pack:** 6



- Jacket 51250**
- Collar
 - Elastic wrists
 - Double storm flap
 - Hook and loop closure
 - Sizes:** S - 5XL
 - Case Pack:** 6



- Pant 51300 Pant**
- Elastic waist
 - Elastic ankles.
 - Sizes:** M-4X
 - Case Pack:** 6




- Coverall 51130**
- Hood
 - Storm flap over zipper
 - Elastic face
 - Elastic wrists and ankles
 - Sizes:** S - 5XL
 - Case Pack:** 6



- Coverall 51150**
- Hood
 - Storm flap over zipper
 - Elastic face and wrists
 - Attached boots
 - Sizes:** S - 5XL
 - Case Pack:** 6



- Apron 51730**
- Long sleeve
 - Elastic wrists
 - 32" length
 - Sizes:** S-4X
 - Case Pack:** 12



- Boot Covers 51740**
- Elastic top
 - 17" high
 - Sizes:** One size
 - Case Pack:** 12 pair



800-645-9291 | 256-350-3873

Email: info@lakeland.com

www.lakeland.com