

Turbo Mixer

LW Scientific offers you two versions of the very popular Turbo Mixers. Ideal for the quick and complete mixing of samples, our cup and platform models will bring convenience and efficiency to your lab. They come with a variable speed control of up to 3000 RPM and can be activated to vibrate continuously or by pressure to the head. The high quality motor comes with a one year warranty and has been designed to offer quiet and vibration free vortex mixing action.

FEATURES

- Suction cup feet
- Metal construction
- Motor fan
- Compact and durable design
- Variable speed control
- Vibration-free
- High quality motor

SPECIFICATIONS

Speed: 3000 RPM
110V / 60Hz (220V available)

CONTROLS

On / off / touch switch
Power on light

WEIGHT AND DIMS

Height: 170mm (6.7")
Width: 160mm (6.3")
Depth: 130mm (5.2")
Weight: 3.2Kg (7lbs)

MXL-TMV7-7RC1:

Cup head dimensions: 50 x 50 x 25mm
(2 x 2 x 1 inches)

MXL-TMV7-7PL1:

Platform head: 100mm diameter x 25mm height
(4" x 1")



Turbo Mixer

Model #	Description
MXL-TMV7-7RC1	Turbo Mixer - Cup
MXL-TMV7-7PL1	Turbo Mixer - Platform

- Vibration-free
- Variable Speed
- Continuous Operation or Touch Control



P 770.270.1394
F 770.270.2389

865 Marathon Parkway
Lawrenceville GA 30046

LWScientific.com