

## Explosion Proof Fluorescent Lights for Paint Booths - 4 foot - 4 lamp

Part #: EPL-48-4L



### Made in the USA

The Larson Electronics EPL-48-4L Explosion Proof Fluorescent Light Fixture is U.S./Canada U.L. approved Class 1 Division 1, Class 1 Division 2 and ideal for hazardous locations where flammable petrochemical vapor or combustible dust exists or has the potential to exist. The unit has a T6 temperature rating and is approved for paint spray booths.

**\*\*\*PLEASE NOTE: ANY FREE SHIPPING OFFERS DO NOT APPLY TO THIS HAZARDOUS LOCATION LIGHT FIXTURE\*\*\***


The EPL-48-4L is our 4 foot long, 4 lamp, UL listed Class 1 Division 1 and Class 2 Division 1 & 2 explosion proof fluorescent light which is also approved for use in paint spray booth applications. This T6 temperature rated fixture comes standard with four fluorescent lamps. This fixture is multi-voltage capable with 347 Volt and 480 Volt versions available upon request. The EPL-48-4L provides operators in hazardous locations with a powerful and affordable lighting solution that provides the best explosion proof protection available without sacrificing fixture durability.



[Click Photo to Enlarge](#)



[Click Photo to Enlarge](#)



[Click Photo to Enlarge](#)

**NOTE ON LAMPS:** We offer a choice of bulbs with all of our explosion proof fluorescent fixtures. However, we standardize on the T-5HO bulbs mostly for longevity and high output. However, many of our customers, including Naval bases, shipyards, oil rigs and petrochemical processing plants operate in very cold conditions, and T-12HO bulbs operate well in those environments. The T12VHO, 110 watt Very High Output lamps make this fixture an ideal replacement for 400 watt metal halide surface mount fixtures in hazardous location areas requiring Class 1 Division 1 rated lights. \*However, the 110 watt T12VHO lamp configuration is not appropriate for paint spray booth applications.

**Mounting options:** Standard surface mounting via our L-brackets attached to Unistruts. Pendant mounting is available for greater distancing of the fixture from the mounting surface (upon request) The Unistrut is attached to our standard L-bracket mounts. These L-bracket mounts can be adjusted to create angle mounts. As illustrated in the photos above, the series of mounting holes at the top of the bracket enable this explosion proof light to be attached to any wall, ceiling or floor surface. A simple through bolt can be used to secure the light to the surface. A single junction box at one end of the light is provided for the electrical connection.

**Suggested Applications:** Paint spray booths, Aircraft maintenance, Oil drilling rigs, Refineries, Solvent and cleaning areas, Gas processing plants, Chemical manufacturing, Waste treatment plants, Gas processing plants.

#### Made in USA Quality

1. Each unit dialectically tested.
2. Fixture arrives assembled and lamped to reduce installation time and cost. Adjustable mounting brackets enable the operator to choose any mounting angle for the fixture, where other models may only offer one or three choices.
3. Fixture constructed of extruded corrosion resistant copper free aluminum alloy.
4. Over-sized, finned ballast housing for 800 mA fixtures provides more heat dissipation and extends ballast life. Larger ballast box accommodates High Output lamp ballasts. Ballast housing easily accessible and externally mounted. Top and bottom covers secured with nuts and bolts, instead of threaded through holes, which can be damaged with dirt.
5. Heavy gauge extruded aluminum reflectors with high gloss reflective finish. Resists dents and corrosion.
6. A wrench is used to unscrew the end caps for relamping the fixture, while other models require the "tap and knock off" method to loosen the end cap.
7. Explosion proof, impact and heat resistant Pyrex tubes provide lamp protection.
8. Spring loaded sockets on both ends hold lamps firmly for maximum shock and vibration protection.

#### Lamp Options

**F54T5HO-850** – 54 watt, 5000 lumens per bulb, 20,000 hour life, 5000 Kelvin color (Suffix –T5)

**F48T12HO-CW** – 60 watt, 4050 lumens per bulb, 12,000 hours life, 4100 Kelvin color (Suffix –T12HO)

**F32T8-841** – 32 watt, 2950 lumens per bulb, 24,000 hours life, 4100 Kelvin color (Suffix –T8)

**F48-T8/HO** - 48 watt, 4000 lumens per bulb, 18,000 hours life, 4100 Kelvin color (Suffix -T8HO)

**T12HO** with magnetic ballast for high heat configurations (hot box explosion proof light applications) - 60 watt, 4050 lumens per bulbs - This bulb, ballast and wiring configuration is designed for application to 165 degrees C.

**F48-T12-D-HO** – 60 watt, 4050 lumens per bulb, 12,000 hours life, 5100 Kelvin color (76 CRI - Color Rendition) - This specialty lamp is designed to mimic daylight conditions. For paint spray booth operators requiring a brighter color light than a traditional "cool white", this bulb can be useful. (Suffix –T12DHO)

**F-48-T12-VHO** – 110 watt, 7000 lumens per bulb, 12,000 hours life, 4200 Kelvin color (Suffix –T12VHO) NOTE: the 110 watt lamps raise the temperature rating from T5 to T6, which is NOT appropriate for paint spray booth applications. The fixture is still Class 1 Division 1 rated, however, this fixture is no longer paint spray booth certified with the 110 watt Very High Output lamp.

**Specifications / Additional Information****EPL-48-4L Explosion Proof****UL Listing:** United States - Canada**Dimensions:** W-24.90" L-57.76" H-9.70"**Weight:** 130 Lbs**Total Watts:** \*216 watts**Voltage:** Multi- 120V-60hz 220V-50hz 240V-60hz 277V-60hz: 347 Volts and 480 Volts available upon request.**Total Lumens:** **STD-T5-HO Bulbs** 20,000**Lamp Life Expectancy:** **STD-T5-HO Bulbs** 20,000 Hours**Efficiency:** **STD-T5-HO Bulbs** 92 Lumens per Watt**Ambient Operating Temp Range:** -30 to 70 C**Beam Angle:** N/A**Color Temp:** 5000K - T5-HO Bulbs**Mounting:** Unistruts - surface mount**Wiring Hub:** 1/2 inch threaded**U.L Approval:** U.S Certificate Canada Certificate**Operating Temp Rating:** T6 Rated**Minimum Operating Temp:** -30 C**Maximum Case Temp:** 90 C

\*Substitution of included standard bulbs for higher output lamps may affect paint spray booth approval.

\*Wattage totals are lamps only and may vary with different lamps.

\*Temperatures above 65 degrees C will diminish ballast life from 5 years to 3 years)

\*5 year warranty replacement on this LED light (or LED bulbs for light fixtures with removable LED bulbs). After 30 days, the customer ships the failed LED light and/or LED bulb to Larson Electronics at their expense. If the failure is a manufacturer defect, we will ship a new replacement to the customer. If failure occurs within 30 days of receipt, Larson Electronics will provide a return label via email to the customer. When the failed light is returned, Larson Electronics will ship a new replacement. Please click here to see our 5 Year Warranty pamphlet.

**Scroll Down to Purchase- Please note: 3 day lead time on this light.**

Part #: [EPL-48-4L \(1857\)](#)

**U.L. Ratings**

Class 1 Div 1 &amp; 2, Groups C &amp; D

Class 1 Div 2, Group A,B,C,D

UL 595 Outdoor Marine Type (Saltwater)

UL 844, 924

UL 1598 Marine Type

Class 2 Division 1- 2, Groups E,F,G

UL Certified Canadian Standards

UL listed for Paint Spray Booths\*

California Title 24 Compliant

**Special Orders- Requirements****Phone:** 1-214-616-6180**Toll Free:** 1-800-369-6671**Fax:** 1-903-498-3364**E-mail:** sales@larsonelectronics.com





Links (Click on the below items to view):

- [SpecSheet French](#)
- [SpecSheet Arabic](#)
- [SpecSheet Spanish](#)
- [Dimensional Drawing](#)
- [Manual](#)

- IES
- STEP
- EASM
- Hi Res Image 1 - Front view of the Fluorescent Light Fixture with T5HO Bulbs
- Hi Res Image 2 - Back of the Fluorescent Fixture
- Hi Res Image 3 - Side view of the Fluorescent Fixture
- Hi Res Image 4 - Front view of the Fluorescent Light Fixture with T8 Bulbs