

Enclosures with Safety Interlock

>> [Hydra-Lift Drum Roller Video](#) <<

### Enclosures with Safety Interlock Help You Comply with OSHA Requirements

( [Hydra-Lift Drum Rollers](#) Sold Separately )


Enclosures for Morse Hydra-Lift Drum Rotators have a safety interlock to automatically shut off the drum roller when the gate is opened. Open the enclosure gate, secure your upright drum on the base plate, then close the gate to allow operation.

Outside post-to-post Dimensions: L88" W40" H63.25" (224 x 102 x 161 cm)




Install all Morse Drum Rotators in accordance with OSHA requirements for enclosure and safety interlock, etc. Drum roller automatically turns off when enclosure door is opened.

For OSHA compliance, see OSHA subpart O.1910.212(a)(4) "Barrels, containers, and drums. Revolving drums, barrels, and containers shall be guarded by an enclosure which is interlocked with the drive mechanism, so that the barrel, drum, or container cannot revolve unless the guard enclosure is in place."

Power connections and motor controls must comply with applicable codes.



**Guard Enclosure is shown below with Drum Roller and Controls that are Sold Separately**





Guard Enclosure Kit	Fits Model # (sold separately)	Gate Switch	Domestic Ship Weight	Domestic Ship Dimensions
GEK-456-1	456-1	AC	400 Lb. (181 kg)	L101" W31" H66" (257 x 79 x 168 cm)
	456-1-50			
GEK-456-3	456-3	AC	400 Lb. (181 kg)	L101" W31" H66" (257 x 79 x 168 cm)
	456-3-575			
	456-3-50			
GEK-456-E1	456-E1	AC Explosion proof *	450 Lb. (205 kg)	L101" W31" H66" (257 x 79 x 168 cm)
	456-E1-50			
GEK-456-E3	456-E3	AC Explosion proof *	450 Lb. (205 kg)	L101" W31" H66" (257 x 79 x 168 cm)
	456-E3-50			
GEK-456-A	456-A	Air Switch	400 Lb. (181 kg)	L101" W31" H66" (257 x 79 x 168 cm)

\* Explosion Proof rated for Class I Group D, and Class II Groups F and G

**Dimensions**

91.4 cm (36") WIDE DOOR OPENING  
 WITH KNOB BOTH SIDES



MADE  
 IN  
 USA

Parts List			
Qty.	Width	Height	Description
1	3' 0" (91 cm)	5' 0" (152 cm)	Wire Mesh Panel
2	7' 0" (213 cm)	5' 0" (152 cm)	Wire Mesh Panel
1	2' 10-7/8" (89 cm)	5' 0" (152 cm)	Hinge Door
4	2" (61 cm)	5' 3.25" (161 cm)	Corner Post

Please contact your Morse dealer