

ATTIX 33 & 44

Superior Dust Extraction

- for safe and professional cleaning



Dust Extractors for Every Application

- hard work shouldn't be harder than it has to be

ATTIX 33 & 44 wet/dry models were built with real working applications in mind to deliver high performance, increased productivity and lower maintenance costs. InfiniClean™ filter cleaning technology automatically cleans the filter every 15 seconds to keep the working environment dust free.

These dust extractors pack high suction power, provide optimal safety and maximum filtration, all while including several other user benefits designed to meet tough requirements in building & construction and other industries.

These powerful machines are reliable and simple to use with safe and ergonomic dust disposal to complete the job.



Multiple Filtration Options

- a solution for every task

ATTIX 33 & 44 dust extractors feature 3-stage filtration technology for the highest level of safety, prolonging the life of the HEPA filter. Filtration ensures potentially hazardous dust stays in the machine, not in the working environment.

Features and Benefits:

- InfiniClean system automatically cleans the filter during operation using reversed air-flow pulse, while continuing constant high performance
- Reduces downtime significantly, as container can be filled without filter maintenance, even in demanding fine dust applications
- Durable and washable PTFE filter that ensures filtration efficiency of fine dust particles - minimum 99.9%
- Same filter used for wet and dry collection
- High air velocity in hose and nozzle
- Optional motor cooling filter, exhaust air collector and long-life filter bag
- Easy service and low maintenance cost



Practical Features

- details to make any job easier

ATTIX 33 & 44 dust extractors are professional, easy-to-handle machines, taking health and safety to a new level. The following features aid in meeting the requirements of professionals working with fine dust in a range of industries.



UNIVERSAL TOOLBOX MOUNT

An optional toolbox mount is available to accommodate a variety of toolboxes.

FLAT TOP FOR STORAGE

A stable and secure place for storing safety gear, accessories or power tools when not in use.



AUTOMATIC TOOL START

By plugging your power tool directly into the ATTIX machine, dust extraction is activated by simply starting your tool. Extraction continues for a few seconds after you power-off your tool to ensure total dust containment.

ROBUST CONTAINER

Durable, double-walled construction ensures a long life, even in the toughest environments.



EASY STORAGE FOR HOSE & CABLE

Easy-to-use hooks and flexible rubber straps for simple and quick storage and transportation.

DURABLE DESIGN

Large wheels, locking swivel casters and optional handle make for easy maneuverability.



Technical Specifications

DESCRIPTION	UNIT	ATTIX 33-01 IC	ATTIX 33-21 IC	ATTIX 44-21 IC
Part Number, Standard Machine	-	107412120	107412122	107412125
Part Number, HEPA Machine	-	900146	900147	900148
Power @ 60 Hz	HP (W)	1.34 (1000)	1.2 (890)	1.2 (890)
Power @ 60 Hz - tool start	HP (W)	-	0.74 (550)	0.74 (550)
Waterlift, max.	in. (mm) H ₂ O	92 (2337)	92 (2337)	92 (2337)
Airflow, max.	CFM (L/min)	148 (4190)	148 (4190)	148 (4190)
Current, max.	amps	8.3	7.4	7.4
Current, max - tool start	amps	-	4.6	4.6
Container Capacity, dry	gal. (L)	8 (30)	8 (30)	11 (42)
Container Capacity, wet	gal. (L)	5.2 (19.5)	5.2 (19.5)	7.8 (29.5)
Dimensions (L x W x H)	in. x in. x in. (mm x mm x mm)	32 x 16 x 25 (800 x 400 x 640)	32 x 16 x 25 (800 x 400 x 640)	32 x 16 x 28 (800 x 400 x 720)
Weight, shipping	lbs. (kg)	45 (20.5)	45 (20.5)	49 (22)
Hose/Tube Diameter	mm	32	32	32
Noise Level @ working distance of 3m	dB(A)	69	69	69
Electrical Approval	-	ETL-C	ETL-C	ETL-C

FEATURES

	InfiniClean	InfiniClean	InfiniClean
Filter Cleaning System	InfiniClean	InfiniClean	InfiniClean
Soft Start	●	●	●
Speed Control	●	●	●
Automatic Tool Start		●	●
Accessory/Tool Storage	●	●	●
Antistatic Hose		●	●
Cable Wrap	●	●	●

ACCESSORIES

Washable PTFE Main Filter	● (Part # 107413540)	● (Part # 107413540)	● (Part # 107413540)
HEPA Filter Cover Kit	○ (Part # 107413542)	○ (Part # 107413542)	○ (Part # 107413542)
Replacement HEPA Filter	○ (Part # 107413555)	○ (Part # 107413555)	○ (Part # 107413555)
Plastic Disposal Bag	● (Part # 107417821)	● (Part # 107417821)	● (Part # 107417821)
Replacement Hose with Hand Tube (Gray)	● (Part # 107409976)		
Replacement A/S Hose		● (Part # 107413543)	● (Part # 107413543)
Replacement Tool Adapter	● (Part # 107409977)	● (Part # 302000535)	● (Part # 302000535)
Optional Storage Box	○ (Part # 107413554)	○ (Part # 107413554)	○ (Part # 107413554)
Toolbox Mounting Kit	○ (Part # 107413551)	○ (Part # 107413551)	○ (Part # 107413551)
18" Floor Nozzle with Height Adjustment	● (Part # 15349)	● (Part # 15349)	● (Part # 15349)
12" Crevice Nozzle	● (Part # 6084)	● (Part # 6084)	● (Part # 6084)

Specifications and details are subject to change without prior notice.

● Standard ○ Optional

Nilfisk, Inc., Industrial Vacuum Division
 740 Hemlock Rd. · Morgantown, PA · 19543
 Tel.: (800) 645-3475 · Fax: (888) 624-8141
 questions@nilfisk.com
 www.nilfiskvacuum.com

