

MILESYN SB 10W30

SYNTHETIC BLEND GF- 5/SN MOTOR OIL

SYNTHETIC BLEND MOTOR OIL 10W30 GF-5 are specially formulated using synthetic and Group II base oils and high performance additive packages to provide superior performance in gasoline fueled and flex-fueled engines. These oils are formulated for excellent oxidation stability and low temperature properties to insure protection during cold starts.

MILES PREMIUM SYNTHETIC BLEND GF-5 engine oils exceed the requirements of ILSAC GF-5 and are "Resource Conserving" for improved fuel economy.

Features and Benefits

- Uniquely formulation proven to help extend engine life
- Proven protection against sludge and engine wear
- Helps prevent the formulation of sludge and harmful deposits
- Contains frictional reducing additives
- Certified as API SN / Resource Conserving

Recommended for Applications

- ILSAC GF-5
- API SN, SM, SL, SJ
- Ford WSS-M2C946-A
- Ford WSS-M2C945-A
- GM 6094M

Applications

SYNTHETIC BLEND MOTOR OIL 10W30 GF-5 are designed to protect and enhance today's modern engines. These fluids can be used in both North American and European gas powered cars requiring the latest GF-5/SN motor oil.

Typical Properties

Density	7.2
Viscosity, cSt @ 100°C	10.4
Viscosity, cSt @ 40°C	68
Viscosity, CCS, cP @ °C	6000 (-25)
Viscosity Index	140
Flash Point, PMCC °C	200
Pour Point, °C	-32
Zinc, Wt. (%)	0.085
Phosphorous, Wt. (%)	0.077
NOACK, Wt. (%)	14.5
HT/HS, Cp @150°C	3