

NPP-4840-FP-E6CD-FDA

48x40 (Standard) Plastic Industrial Pallet




Technical Data

Dimensions	48x40x6.1 inches (1219x1016x155 mm)
Weight	40.0 lbs
Load Capacities	
Static	8800 lbs
Dynamic	4400 lbs
Racking	2200 lbs
Entry	4-way
Pallets per Stack	17
Truckload Qty	510

Available in Truckload or LTL quantities. Minimum quantity required. We reserve the right to change any stated information without prior notice. Not responsible for typographical errors.

Handling Data

Nestable No	Reusability Multi-Trip	ISPM-15 Exempt Yes
Stackable Yes	Destination Captive	Food Grade FDA Approved
Rackable Yes	Airfreight Yes	Pharmaceutical Yes



DECK & BOTTOM SUPPORT OPTIONS

Open or Closed Deck

3 Runner or 6 Runner



Materials and Colors

Condition
New

Material
HDPP

Color
Blue

(Virgin)

Deck Specs

Top Deck
Closed

Bottom Deck
6-Runner

Available Options:
RFID Transponders
Individual Markings
Anti-Slip Bottom Grommets
ESD Prevention for Anti-Static
FDA Version with Freezer Additives
Rod Inserts for Increased Performance.

Features

Ideal for closed loops or distribution chains across industry sectors including Food, Retail, Medical and Pharmaceutical.

- High performance at low cost
- Top Safety Rim
- Allows for safe double stacking
- Low-cost Plastic Pallet
- Impervious to acids, fats, solvents and odors
- Resists water absorption & bacteria growth
- Inert to infestation, mold and mildew
- Consistently dimensionally accurate
- Exempt from ISPM 15 shipping regulations



Your Sales Rep
Mike Cunneen
mcunneen@nelsoncompany.com
M 804.307.1474

NelsonTM

The Nelson Company

www.NelsonCompany.com

www.NelsonTechCenter.com