

Issue Date 09-Jan-2015

Revision Date 09-Jan-2015

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Bacterial Enzyme Odor Eliminator

Other means of identification

Product Code 640410

Synonyms None

Details of the supplier of the safety data sheet

Company Name Global Industrial
2505 Mill Center Parkway, Buford, GA 30518
(888) 978-7759

Emergency telephone number

Emergency Telephone Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Carcinogenicity	Category 1B

Label elements

Emergency Overview

Danger

Hazard statements

May cause cancer



Appearance White Cloudy

Physical state Liquid

Odor Fresh & Clean

Precautionary Statements - Prevention

Obtain special instructions before use
Do not handle until all safety precautions have been read and understood
Use personal protective equipment as required

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Nonylphenol Ethoxylate	9016-45-9	1-5	*
Sodium Nitrate	7631-99-4	.1-1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**First aid measures****Skin Contact**

Wash skin with soap and water.

Eye contact

Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.

Inhalation

Remove to fresh air.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed**Symptoms**

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed**Note to physicians**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES**Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.**Specific hazards arising from the chemical**

No Information available.

Explosion data**Sensitivity to Mechanical Impact** None.**Sensitivity to Static Discharge** None.**Protective equipment and precautions for firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures**

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection No special technical protective measures are necessary.

Skin and body protection No special technical protective measures are necessary. Wear protective gloves and protective clothing. Prolonged contact may cause redness and irritation. Wear protective gloves and protective clothing if needed.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	White Cloudy
Color	White
Odor	Fresh & Clean
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	6.5 - 7.5	

Specific Gravity	0.999
Viscosity	< 25 cP @ 25°C
Melting point/freezing point	No Information available
Flash point	None
Boiling point / boiling range	210 ° F
Evaporation rate	No Information available
Flammability (solid, gas)	
Flammability Limits in Air	
Upper flammability limit:	No Information available
Lower flammability limit:	No Information available
Vapor pressure	No Information available
Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	8.32
VOC Content (%)	< 0.1

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Product Information	No data available Harmful by inhalation, ingestion, in contact with eyes and skin.
Inhalation	No data available. May cause irritation of respiratory tract. May cause possibly severe irritation of the respiratory tract.
Eye contact	No data available. Contact with eyes may cause irritation. Contact with eyes may cause irritation or burns. Contact with eyes may cause severe irritation and possible chemical burns. Direct contact can cause corrosive ocular burns.
Skin Contact	No data available. May be absorbed through the skin in harmful amounts. Prolonged contact may cause redness and irritation. May cause severe irritation or burns to the skin. Prolonged or repeated contact may cause absorption to the skin. Contact causes severe skin irritation and possible burns. Prolonged or repeated contact may dry skin and cause irritation. May cause severe pain with brownish or yellowish stains. Burns may penetrate the skin with sharply defined edges and heal slowly with scar formation. Contact is irritating and may cause an unusual, skin rash that appears similar to ballooning of the skin. If skin is moist, formation of hydrofluoric acid can cause serious burns. These burns do not appear serious at first, but may cause severe damage if not treated immediately.

Ingestion

No data available. May cause gastro intestinal irritation. Harmful if swallowed. Ingestion may cause digestive tract irritation or corrosion, nausea and possibly bloody vomiting, bloody diarrhea and abdominal pain.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Sodium Nitrate 7631-99-4	= 1267 mg/kg (Rat)	Yes	Yes

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No Information available.

Germ cell mutagenicity No Information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Sodium Nitrate 7631-99-4	Yes	Group 2A	Yes	X

IARC (International Agency for Research on Cancer)

Group 2A - Probably Carcinogenic to Humans

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.

STOT - single exposure No Information available.

STOT - repeated exposure No Information available.

Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

12. ECOLOGICAL INFORMATION

Ecotoxicity

0% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Nonylphenol Ethoxylate 9016-45-9	Yes	5: 96 h Fish mg/L LC50	Yes
Tetrasodium EDTA 64-02-8	1.01: 72 h <i>Desmodesmus subspicatus</i> mg/L EC50	41: 96 h <i>Lepomis macrochirus</i> mg/L LC50 static 59.8: 96 h <i>Pimephales promelas</i> mg/L LC50 static	610: 24 h <i>Daphnia magna</i> mg/L EC50
Sodium Nitrate 7631-99-4	Yes	2000: 96 h <i>Lepomis macrochirus</i> mg/L LC50 static 994.4 - 1107: 96 h <i>Oncorhynchus mykiss</i> mg/L LC50 static	Yes

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
Sodium Nitrate 7631-99-4	-3.8

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
Sodium Nitrate 7631-99-4	Toxic Ignitable Reactive

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania

Sodium Nitrate 7631-99-4	X	X	X
-----------------------------	---	---	---

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 0	Flammability 0	Physical hazards 0	Personal protection A

Issue Date 09-Jan-2015
Revision Date 09-Jan-2015

Revision Note
 No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet