

## 1. PRODUCT AND COMPANY IDENTIFICATION

**Product identifier**

**Product Name** Ultra High Speed Floor Finish

**Other means of identification**

**Product Code** 640403  
**Synonyms** None

**Details of the supplier of the safety data sheet**

**Company Name** Global Industrial  
2505 Mill Center Parkway, Buford, GA 30518  
(888) 978-7759

**Emergency telephone number**

**Emergency Telephone** Chemtrec (US & Canada) 800-424-9300  
Chemtrec (outside US & Canada) 703-527-3887

## 2. HAZARDS IDENTIFICATION

**Classification**

**OSHA Regulatory Status**

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified

**Label elements**

**Emergency Overview**

**Appearance** White Emulsion

**Physical state** Liquid

**Odor** Typical Acrylic Polymer

**Precautionary Statements - Response**

Immediately call a POISON CENTER or doctor/physician  
Specific Treatment (See Section 4 on the SDS)

**Precautionary Statements - Disposal**

Disposal should be in accordance with applicable regional, national and local laws and regulations

**Hazards not otherwise classified (HNOC)**

**Other Information**

- Harmful to aquatic life with long lasting effects
- Harmful to aquatic life

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
---------------	---------	----------	--------------

Tributoxyethyl Phosphate	78-51-3	1-5	*
--------------------------	---------	-----	---

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

#### 4. FIRST AID MEASURES

##### First aid measures

<b>Skin Contact</b>	Wash off immediately with plenty of water. Wash skin with soap and water.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water.

##### Most important symptoms and effects, both acute and delayed

<b>Symptoms</b>	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

##### Indication of any immediate medical attention and special treatment needed

<b>Note to physicians</b>	Treat symptomatically.
---------------------------	------------------------

#### 5. FIRE-FIGHTING MEASURES

##### Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Caution: Use of water spray when fighting fire may be inefficient.

##### Specific hazards arising from the chemical

No Information available.

##### Explosion data

**Sensitivity to Mechanical Impact** None.

**Sensitivity to Static Discharge** None.

##### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

#### 6. ACCIDENTAL RELEASE MEASURES

##### Personal precautions, protective equipment and emergency procedures

<b>Personal precautions</b>	Ensure adequate ventilation, especially in confined areas.
-----------------------------	--

##### Environmental precautions

<b>Environmental precautions</b>	See Section 12 for additional ecological information.
----------------------------------	---

##### Methods and material for containment and cleaning up

<b>Methods for containment</b>	Prevent further leakage or spillage if safe to do so.
<b>Methods for cleaning up</b>	Pick up and transfer to properly labeled containers.

#### 7. HANDLING AND STORAGE

##### Precautions for safe handling

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place.

**Incompatible materials** None known based on information supplied.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control parameters**

**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-methoxypropoxy)propano 34590-94-8	STEL: 150 ppm TWA: 100 ppm S*	TWA: 100 ppm TWA: 600 mg/m <sup>3</sup> (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m <sup>3</sup> (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m <sup>3</sup> (vacated) S* S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m <sup>3</sup> STEL: 150 ppm STEL: 900 mg/m <sup>3</sup>

NIOSH IDLH *Immediately Dangerous to Life or Health*

**Other Information** Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

**Appropriate engineering controls**

**Engineering Controls** Showers, Eyewash stations & Ventilation systems.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin and body protection** Wear protective gloves and protective clothing.

**Respiratory protection** If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

**General Hygiene** Handle in accordance with good industrial hygiene and safety practice.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

**Information on basic physical and chemical properties**

**Physical state** Liquid  
**Appearance** White Emulsion  
**Color** White  
**Odor** Typical Acrylic Polymer  
**Odor threshold** No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	8.0 - 9.0	
Specific Gravity	1.03	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		

<b>Upper flammability limit:</b>	No Information available
<b>Lower flammability limit:</b>	No Information available
<b>Vapor pressure</b>	No Information available
<b>Vapor density</b>	No Information available
<b>Water solubility</b>	Emulsifies
<b>Partition coefficient</b>	No Information available
<b>Autoignition temperature</b>	No Information available
<b>Decomposition temperature</b>	No Information available

**Other Information**

<b>Density Lbs/Gal</b>	8.56
<b>VOC Content (%)</b>	2.823

**10. STABILITY AND REACTIVITY****Reactivity**

No data available

**Chemical stability**

Stable under recommended storage conditions.

**Possibility of Hazardous Reactions**

None under normal processing.

**Conditions to avoid**

Extremes of temperature and direct sunlight.

**Incompatible materials**

None known based on information supplied.

**Hazardous Decomposition Products**

None known based on information supplied.

**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information**

<b>Inhalation</b>	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
<b>Eye contact</b>	Avoid contact with eyes. Contact with eyes may cause irritation.
<b>Skin Contact</b>	Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation.
<b>Ingestion</b>	Do not taste or swallow. Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Tributoxyethyl Phosphate 78-51-3	= 3 g/kg ( Rat )	> 16 mL/kg ( Rabbit )	> 6.4 mg/L ( Rat ) 4 h

**Information on toxicological effects**

**Symptoms** No Information available.

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Sensitization</b>	No Information available.
<b>Germ cell mutagenicity</b>	No Information available.
<b>Carcinogenicity</b>	No Information available.
<b>Reproductive toxicity</b>	No Information available.
<b>STOT - single exposure</b>	No Information available.

**STOT - repeated exposure** No Information available.  
**Aspiration hazard** No Information available.

#### Numerical measures of toxicity - Product Information

**Unknown Acute Toxicity** 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

**ATEmix (oral)** 8,048.00  
**ATEmix (dermal)** 35,928.00  
**ATEmix (inhalation-dust/mist)** 265.73

## 12. ECOLOGICAL INFORMATION

### Ecotoxicity

23.62685688% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Tributoxyethyl Phosphate 78-51-3	-	10.4 - 12.0: 96 h Pimephales promelas mg/L LC50 flow-through	-
2-(2-ethoxyethoxy)ethanol 111-90-0	-	10000: 96 h Lepomis macrochirus mg/L LC50 static 19100 - 23900: 96 h Lepomis macrochirus mg/L LC50 flow-through 13400: 96 h Salmo gairdneri mg/L LC50 flow-through 11400 - 15700: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 11600 - 16700: 96 h Pimephales promelas mg/L LC50 flow-through	3940 - 4670: 48 h Daphnia magna mg/L EC50
[2-(2-Methoxymethylethoxy)methylthoxy]-propanol 25498-49-1	-	11619: 96 h Pimephales promelas mg/L LC50 static	10: 48 h Daphnia magna mg/L EC50
2-(2-methoxypropoxy)propano 34590-94-8	-	10000: 96 h Pimephales promelas mg/L LC50 static	1919: 48 h Daphnia magna mg/L LC50
Methyl Chloro Isothiazolinone 26172-55-4	0.11 - 0.16: 72 h Pseudokirchneriella subcapitata mg/L EC50 static 0.03 - 0.13: 96 h Pseudokirchneriella subcapitata mg/L EC50 static 0.31: 120 h Anabaena flos-aquae mg/L EC50	1.6: 96 h Oncorhynchus mykiss mg/L LC50 semi-static	4.71: 48 h Daphnia magna mg/L EC50 0.12 - 0.3: 48 h Daphnia magna mg/L EC50 Flow through 0.71 - 0.99: 48 h Daphnia magna mg/L EC50 Static
Magnesium Chloride 7786-30-3	2200: 72 h Desmodesmus subspicatus mg/L EC50	1970 - 3880: 96 h Pimephales promelas mg/L LC50 static 4210: 96 h Gambusia affinis mg/L LC50 static	140: 48 h Daphnia magna mg/L EC50 Static 1400: 24 h Daphnia magna mg/L EC50

### Persistence and degradability

No Information available.

### Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
Tributoxyethyl Phosphate 78-51-3	3.65 - 4.78

**Other adverse effects** No Information available

## 13. DISPOSAL CONSIDERATIONS

### Waste treatment methods

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

#### 14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

**DOT** Not regulated

**TDG** Not regulated

#### 15. REGULATORY INFORMATION

##### International Inventories

**TSCA** Complies

**DSL/NDSL** Complies

##### Legend:

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

##### US Federal Regulations

##### SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-ethoxyethoxy)ethanol - 111-90-0	1.0
[2-(2-Methoxymethylethoxy)methylethoxy]-propanol - 25498-49-1	1.0
Zinc ammonium carbonate -	1.0

##### SARA 311/312 Hazard Categories

<b>Acute health hazard</b>	No
<b>Chronic Health Hazard</b>	No
<b>Fire hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

##### CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

##### CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

##### US State Regulations

##### California Proposition 65

This product has been evaluated and does not require warning labeling under California Proposition 65.

##### U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-ethoxyethoxy)ethanol 111-90-0	X	-	X
[2-(2-Methoxymethylethoxy)methylethoxy]-propanol	X	-	X

25498-49-1			
Zinc ammonium carbonate	X	-	X
Magnesium Nitrate 10377-60-3	X	X	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not Applicable

**16. OTHER INFORMATION**

<b>NFPA</b>	Health hazards 0	Flammability 0	Instability 0	Physical and Chemical Properties Yes
<b>HMIS</b>	Health hazards 0	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 13-Mar-2017  
 Revision Date 13-Mar-2017

Revision Note  
 No Information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**