

Issue Date 08-Jan-2015

Revision Date 08-Jan-2015

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION**Product identifier****Product Name** Multi-Purpose Cleaner & Protectant**Other means of identification****Product Code** 640415**Synonyms** None**Details of the supplier of the safety data sheet****Company Name** Global Industrial
2505 Mill Center Parkway, Buford, GA 30518
(516) 608-3000**Emergency telephone number****Emergency Telephone** Chemtrec (US & Canada) 800-424-9300
Chemtrec (outside US & Canada) 703-527-3887**2. HAZARDS IDENTIFICATION****Classification****OSHA Regulatory Status**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Flammable liquids	Category 4

Label elements**Emergency Overview****Warning**

Combustible liquid

Appearance Opaque Violet**Physical state** Liquid**Odor** Tutti-Frutti**Precautionary Statements - Prevention**Keep away from heat/sparks/open flames/hot surfaces. — No smoking
Wear protective gloves/protective clothing/eye protection/face protection**Precautionary Statements - Response**Specific Treatment (See Section 4 on the SDS)
In case of fire: Use CO₂, dry chemical, or foam for extinction**Precautionary Statements - Storage**

Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity

1% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-Propanol	67-63-0	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

General advice

If symptoms persist, call a physician.

Skin Contact

Immediate medical attention is not required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. If skin irritation persists, call a physician.

Eye contact

Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing. If symptoms persist, call a physician.

Inhalation

Immediate medical attention is not required. If symptoms persist, call a physician. Move to fresh air in case of accidental inhalation of vapors or decomposition products.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Never give anything by mouth to an unconscious person. Call a physician. Do NOT induce vomiting.

Self-protection of the first aider

Use personal protective equipment as required.

Most important symptoms and effects, both acute and delayed

Symptoms

Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use. Dry chemical. Carbon dioxide (CO₂). Water spray (fog). Alcohol resistant foam.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

Keep product and empty container away from heat and sources of ignition. Risk of ignition.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment as required. Remove all sources of ignition. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Pay attention to flashback. Take precautionary measures against static discharges.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Soak up with inert absorbent material. Dam up. Pick up and transfer to properly labeled containers. Take precautionary measures against static discharges.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use with local exhaust ventilation. All equipment used when handling the product must be grounded. Keep away from heat/sparks/open flames/hot surfaces. — No smoking. Use personal protective equipment as required. Do not breathe dust/fume/gas/mist/vapors/spray. Take necessary action to avoid static electricity discharge (which might cause ignition of organic vapors).

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep containers tightly closed in a cool, well-ventilated place. Keep away from heat. Keep in properly labeled containers.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-Propanol 67-63-0	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m ³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m ³ STEL: 500 ppm STEL: 1225 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Tight sealing safety goggles.

Skin and body protection Wear protective gloves and protective clothing if needed.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene

When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Opaque Violet
Color	Violet
Odor	Tutti-Frutti
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	7.0 - 8.0	
Specific Gravity	0.992	
Viscosity	> 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	72 °C 161 °F	
Boiling point / boiling range	< 212 °F	/
Evaporation rate	No Information available	
Flammability (solid, gas)		
Flammability Limits in Air		
Upper flammability limit:	Not Applicable	
Lower flammability limit:	Not Applicable	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.26
VOC Content (%)	3

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure**Product Information**

Maybe harmful by inhalation, ingestion, in contact with eyes and skin,

Inhalation	Breathing of vapors may cause dizziness and shortness of breath.
Eye contact	Contact with eyes may cause irritation or burns.
Skin Contact	Prolonged or repeated contact may dry skin and cause irritation.
Ingestion	May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-Propanol 67-63-0	= 1870 mg/kg (Rat)	= 4059 mg/kg (Rabbit)	= 72600 mg/m ³ (Rat) 4 h

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No Information available.
Germ cell mutagenicity No Information available.
Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
2-Propanol 67-63-0	Yes	Group 3	Yes	X

IARC (International Agency for Research on Cancer)

Not classifiable as a human carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.
STOT - single exposure No Information available.
STOT - repeated exposure No Information available.
Target organ effects EYES, Respiratory system, Skin.
Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 1% of the mixture consists of ingredient(s) of unknown toxicity
The following values are calculated based on chapter 3.1 of the GHS document .

12. ECOLOGICAL INFORMATION**Ecotoxicity**

1% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-Propanol 67-63-0	1000: 96 h <i>Desmodesmus subspicatus</i> mg/L EC50 1000: 72 h <i>Desmodesmus subspicatus</i> mg/L EC50	9640: 96 h <i>Pimephales promelas</i> mg/L LC50 flow-through 11130: 96 h <i>Pimephales promelas</i> mg/L LC50 static 1400000: 96 h <i>Lepomis macrochirus</i> µg/L LC50	13299: 48 h <i>Daphnia magna</i> mg/L EC50

Sodium Lauryl Sulfate 151-21-3	53: 72 h <i>Desmodesmus subspicatus</i> mg/L EC50 30 - 100: 96 h <i>Desmodesmus subspicatus</i> mg/L EC50 117: 96 h <i>Pseudokirchneriella subcapitata</i> mg/L EC50 3.59 - 15.6: 96 h <i>Pseudokirchneriella subcapitata</i> mg/L EC50 static	8 - 12.5: 96 h <i>Pimephales promelas</i> mg/L LC50 static 15 - 18.9: 96 h <i>Pimephales promelas</i> mg/L LC50 static 22.1 - 22.8: 96 h <i>Pimephales promelas</i> mg/L LC50 static 10.8 - 16.6: 96 h <i>Poecilia reticulata</i> mg/L LC50 static 1.31: 96 h <i>Cyprinus carpio</i> mg/L LC50 semi-static 4.2 - 4.8: 96 h <i>Lepomis macrochirus</i> mg/L LC50 flow-through 4.5: 96 h <i>Lepomis macrochirus</i> mg/L LC50 5.8 - 7.5: 96 h <i>Pimephales promelas</i> mg/L LC50 static 10.2 - 22.5: 96 h <i>Pimephales promelas</i> mg/L LC50 semi-static 6.2 - 9.6: 96 h <i>Pimephales promelas</i> mg/L LC50 13.5 - 18.3: 96 h <i>Poecilia reticulata</i> mg/L LC50 semi-static 4.3 - 8.5: 96 h <i>Oncorhynchus mykiss</i> mg/L LC50 static 4.62: 96 h <i>Oncorhynchus mykiss</i> mg/L LC50 flow-through 4.2: 96 h <i>Oncorhynchus mykiss</i> mg/L LC50 7.97: 96 h <i>Brachydanio rerio</i> mg/L LC50 flow-through 9.9 - 20.1: 96 h <i>Brachydanio rerio</i> mg/L LC50 semi-static 4.06 - 5.75: 96 h <i>Lepomis macrochirus</i> mg/L LC50 static	1.8: 48 h <i>Daphnia magna</i> mg/L EC50
-----------------------------------	--	---	--

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Propanol 67-63-0	0.05

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
2-Propanol 67-63-0	Toxic Ignitable

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-Propanol - 67-63-0	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-Propanol 67-63-0	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 2	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 1	Flammability 2	Physical hazards 0	Personal protection B

Issue Date 08-Jan-2015

Revision Date 08-Jan-2015

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet