



SAFETY DATA SHEET

Issue Date 22-Feb-2017

Revision Date 22-Feb-2017

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Swipe-It!

Other means of identification

Product Code NL212

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This product has been classified in accordance with the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified

Label elements

Emergency Overview

Appearance Clear Blue

Physical state Liquid

Odor Almond

Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician
Specific Treatment (See Section 4 on the SDS)

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)

Other Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-(2-butoxyethoxy)ethanol	112-34-5	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Skin Contact	Wash off immediately with plenty of water. Wash skin with soap and water.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
2-(2-butoxyethoxy)ethanol 112-34-5	TWA: 10 ppm inhalable fraction and vapor	-	-

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Rubber gloves if prolonged contact and/or handling large volumes.

Respiratory protection Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment. If irritation is experienced, move to a well ventilated area.

General Hygiene Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear Blue
Color Blue
Odor Almond
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	10.0 - 12.0	
Specific Gravity	1.002	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	above 200F	
Boiling point / boiling range	100 °C / 212 ° F Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.35
VOC Content (%)	1.5

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Extremes of temperature and direct sunlight.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure****Product Information**

Inhalation	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Avoid contact with eyes. Contact with eyes may cause irritation or burns.
Skin Contact	Avoid contact with skin. Prolonged contact may cause redness and irritation.
Ingestion	Do not taste or swallow. Can burn mouth, throat, and stomach. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-(2-butoxyethoxy)ethanol 112-34-5	= 5660 mg/kg (Rat)	= 2700 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms	No Information available.
-----------------	---------------------------

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No Information available.
Germ cell mutagenicity	No Information available.
Carcinogenicity	No Information available.
Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity	0% of the mixture consists of ingredient(s) of unknown toxicity
-------------------------------	---

12. ECOLOGICAL INFORMATION

Ecotoxicity

0.9% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-(2-butoxyethoxy)ethanol 112-34-5	100: 96 h Desmodemus subspicatus mg/L EC50	1300: 96 h Lepomis macrochirus mg/L LC50 static	100: 48 h Daphnia magna mg/L EC50 2850: 24 h Daphnia magna mg/L EC50
PROPRIETARY	-	1.2: 96 h Oncorhynchus mykiss mg/L LC50	5.3: 48 h Daphnia mg/L LC50

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-(2-butoxyethoxy)ethanol - 112-34-5	1.0

SARA 311/312 Hazard Categories

Acute health hazard

No

Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations**California Proposition 65**

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-(2-butoxyethoxy)ethanol 112-34-5	X	-	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 0	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 1	Flammability 0	Physical hazards 0	Personal protection B

Issue Date 22-Feb-2017

Revision Date 22-Feb-2017

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet