



SAFETY DATA SHEET

Issue Date 12-Oct-2015

Revision Date 22-May-2015

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Qwiks Glass Cleaner Concentrate

Other means of identification

Product Code NL900

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 3
Serious eye damage/eye irritation	Category 2
Flammable liquids	Category 3

Label elements

Emergency Overview

Warning

Hazard statements

Causes mild skin irritation

Causes serious eye irritation

Flammable liquid and vapor



Appearance Clear Blue**Physical state** Liquid**Odor** Alcohol**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection
 Keep away from heat/sparks/open flames/hot surfaces. — No smoking
 Keep container tightly closed
 Ground/bond container and receiving equipment
 Use explosion-proof electrical/ventilating/lighting/equipment.
 Use only non-sparking tools
 Take precautionary measures against static discharge

Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician
 Specific Treatment (See Section 4 on the SDS)
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 If skin irritation occurs: Get medical advice/attention
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 In case of fire: Use CO₂, dry chemical, or foam for extinction

Precautionary Statements - Storage

Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity 0.00126% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
2-Propanol	67-63-0	7-13	*
2-butoxyethanol	111-76-2	1-5	*
Trisodium nitrilotriacetate	5064-31-3	<0.1	*
Sodium Hydroxide	1310-73-2	<0.1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

General advice	Immediate medical attention is required. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).
Skin Contact	Wash off immediately with plenty of water.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.
Self-protection of the first aider	Remove all sources of ignition.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology

Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Remove all sources of ignition. Evacuate personnel to safe areas. Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Dam up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Ensure adequate ventilation, especially in confined areas. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Take precautionary measures against static discharges. Use spark-proof tools and explosion-proof equipment. All equipment used when handling the product must be grounded.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep tightly closed in a dry and cool place. Keep in properly labeled containers.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH

2-Propanol 67-63-0	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m ³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m ³ STEL: 500 ppm STEL: 1225 mg/m ³
2-butoxyethanol 111-76-2	TWA: 20 ppm	TWA: 50 ppm TWA: 240 mg/m ³ (vacated) TWA: 25 ppm (vacated) TWA: 120 mg/m ³ (vacated) S* S*	IDLH: 700 ppm TWA: 5 ppm TWA: 24 mg/m ³
Sodium Hydroxide 1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³ (vacated) Ceiling: 2 mg/m ³	IDLH: 10 mg/m ³ Ceiling: 2 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

- Eye/face protection** Tight sealing safety goggles.
- Skin and body protection** Prolonged or repeated contact may be drying to skin. Rubber gloves if prolonged contact is involved.
- Respiratory protection** Ensure adequate ventilation, especially in confined areas. If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators or air purifying respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene When using do not eat, drink or smoke. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear Blue
Color Blue
Odor Alcohol
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	10.0 - 11.5	
Specific Gravity	0.97	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	34 °C 94 °F	
Boiling point / boiling range	< 212 ° F	/
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	

Autoignition temperature No Information available
Decomposition temperature No Information available

Other Information

Density Lbs/Gal 8.08
VOC Content (%) 14.09

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Maybe harmful by inhalation, ingestion, in contact with eyes and skin,

Inhalation

Avoid breathing vapors or mists. Breathing of vapors may cause dizziness and shortness of breath. Inhalation of vapors in high concentration may cause irritation of respiratory system.

Eye contact

Avoid contact with eyes. Severely irritating to eyes.

Skin Contact

Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation. Prolonged contact with skin may result in the absorption of potentially harmful amounts leading to possible liver and kidney damage.

Ingestion

Do not taste or swallow. May cause gastro intestinal irritation.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
2-Propanol 67-63-0	= 1870 mg/kg (Rat)	= 4059 mg/kg (Rabbit)	= 72600 mg/m ³ (Rat) 4 h
2-butoxyethanol 111-76-2	= 470 mg/kg (Rat)	= 99 mg/kg (Rabbit)	= 450 ppm (Rat) 4 h
Trisodium nitrilotriacetate 5064-31-3	= 1100 mg/kg (Rat)	-	> 5 mg/L (Rat) 4 h
Sodium Hydroxide 1310-73-2	-	= 1350 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms

No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization

No Information available.

Germ cell mutagenicity

No Information available.

Carcinogenicity

This product contains one or more substances which are classified by IARC as carcinogenic to humans (Group I), probably carcinogenic to humans (Group 2A) or possibly carcinogenic to humans (Group 2B). The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
---------------	-------	------	-----	------

2-Propanol 67-63-0	-	Group 3	-	X
2-butoxyethanol 111-76-2	A3	Group 3	-	-
Trisodium nitrilotriacetate 5064-31-3	-	Group 2B	-	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 3 -Not classifiable as a human carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Chronic toxicity	May cause adverse effects on the bone marrow and blood-forming system. May cause adverse liver effects.
Target organ effects	Blood, Central nervous system, EYES, hematopoietic system, Kidney, Liver, Respiratory system, Skin.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0.00126% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral)	9,512.00
ATEmix (dermal)	21,229.00
ATEmix (inhalation-dust/mist)	70.70
ATEmix (inhalation-vapor)	24,064.00

12. ECOLOGICAL INFORMATION

Ecotoxicity

0.00126% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
2-Propanol 67-63-0	1000: 96 h Desmodesmus subspicatus mg/L EC50 1000: 72 h Desmodesmus subspicatus mg/L EC50	1400000: 96 h Lepomis macrochirus µg/L LC50 11130: 96 h Pimephales promelas mg/L LC50 static 9640: 96 h Pimephales promelas mg/L LC50 flow-through	13299: 48 h Daphnia magna mg/L EC50
2-butoxyethanol 111-76-2	-	1490: 96 h Lepomis macrochirus mg/L LC50 static 2950: 96 h Lepomis macrochirus mg/L LC50	1000: 48 h Daphnia magna mg/L EC50 1698 - 1940: 24 h Daphnia magna mg/L EC50
Nonylphenol Ethoxylate 9016-45-9	-	5: 96 h Fish mg/L LC50	-
Tetrasodium EDTA 64-02-8	1.01: 72 h Desmodesmus subspicatus mg/L EC50	59.8: 96 h Pimephales promelas mg/L LC50 static 41: 96 h Lepomis macrochirus mg/L LC50 static	610: 24 h Daphnia magna mg/L EC50
Sodium Hydroxide 1310-73-2	-	45.4: 96 h Oncorhynchus mykiss mg/L LC50 static	-
Trisodium nitrilotriacetate 5064-31-3	560 - 1000: 96 h Chlorella vulgaris mg/L EC50	72 - 133: 96 h Oncorhynchus mykiss mg/L LC50 static 175 - 225: 96 h Lepomis macrochirus mg/L LC50 static 252: 96 h Lepomis macrochirus mg/L LC50 470: 96 h Pimephales promelas mg/L LC50 static 93 - 170: 96 h Pimephales promelas mg/L LC50 flow-through 560 - 1000: 96 h Poecilia reticulata mg/L LC50 semi-static 560 - 1000: 96 h Poecilia reticulata mg/L LC50 114: 96 h Pimephales promelas mg/L LC50 560 - 1000: 96 h Oryzias latipes mg/L LC50 560 - 1000: 96 h Oryzias latipes mg/L LC50 semi-static	560 - 1000: 48 h Daphnia magna mg/L LC50

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Chemical Name	Partition coefficient
2-Propanol 67-63-0	0.05
2-butoxyethanol 111-76-2	0.81

Other adverse effects No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
2-Propanol 67-63-0	Toxic Ignitable
Sodium Hydroxide 1310-73-2	Toxic Corrosive

14. TRANSPORT INFORMATION

According to Exceptions for Class 3 (flammable and combustible liquids), this product maybe reclassified as combustible liquid, see 49CFR173.150(e)(1) and (2).

DOT Not regulated (If shipped in NON BULK packaging by ground transport)
UN/ID No. UN1993
Proper shipping name Flammable liquids, n.o.s.
Hazard Class 3
Packing Group III
Special Provisions B1, B52, IB3, T4, TP1, TP29
Description UN1993, Flammable liquids, n.o.s. (Isopropanol), 3, III
Emergency Response Guide Number 128

TDG
UN/ID No. UN1993
Proper shipping name Flammable liquid, n.o.s.
Hazard Class 3
Packing Group III
Description UN1993, Flammable liquids, n.o.s. (Isopropanol), 3, III

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
2-Propanol - 67-63-0	1.0
2-butoxyethanol - 111-76-2	1.0

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium Hydroxide 1310-73-2	1000 lb	-	-	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Sodium Hydroxide 1310-73-2	1000 lb	-	RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations

California Proposition 65

WARNING: This product contains a chemical known to the state of California to cause cancer.

Chemical Name(s):

Nitilotriacetic acid, Trisodium salt

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
2-Propanol 67-63-0	X	X	X
2-butoxyethanol 111-76-2	X	X	X
Sodium Hydroxide 1310-73-2	X	X	X
Trisodium nitilotriacetate 5064-31-3	-	X	-

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 1	Flammability 3	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 1	Flammability 3	Physical hazards 0	Personal protection B

Issue Date 12-Oct-2015

Revision Date 22-May-2015

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet