



SAFETY DATA SHEET

Issue Date 21-Apr-2017

Revision Date 20-Apr-2017

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name URINAKLEEN

Other means of identification

Product Code NL020

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Category 4
Acute toxicity - Dermal	Not classified
Acute toxicity - Inhalation (Gases)	Category 4
Acute toxicity - Inhalation (Dusts/Mists)	Category 4
Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1
Specific target organ toxicity (single exposure)	Category 3

Label elements

Emergency Overview

Danger

Hazard statements

Harmful if swallowed

Harmful if inhaled

Causes severe skin burns and eye damage

May cause respiratory irritation. May cause drowsiness or dizziness

**Appearance** Clear**Physical state** Liquid**Odor** Acidic**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling
 Do not eat, drink or smoke when using this product
 Use only outdoors or in a well-ventilated area
 Do not breathe dust/fume/gas/mist/vapors/spray
 Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 Immediately call a POISON CENTER or doctor/physician
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 Wash contaminated clothing before reuse
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 Call a POISON CENTER or doctor/physician if you feel unwell
 Immediately call a POISON CENTER or doctor/physician
 IF SWALLOWED: Rinse mouth. DO NOT induce vomiting
 Drink plenty of water
 Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Hydrochloric Acid	7647-01-0	10-30	*
Propargyl Alcohol	107-19-7	<0.1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures**General advice**

Immediate medical attention is required.

Skin Contact

Immediate medical attention is required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. For minor skin contact, avoid spreading material on unaffected skin. For severe burns, immediate medical attention is required.

Eye contact

Immediate medical attention is required. Rinse immediately with plenty of water, also under

the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes.

Inhalation	Remove to fresh air. Call a physician or poison control center immediately. If not breathing, give artificial respiration. If breathing is difficult, give oxygen.
Ingestion	Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Remove from exposure, lie down. Clean mouth with water and drink afterwards plenty of water. Call a physician or poison control center immediately.
Self-protection of the first aider	Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.

Most important symptoms and effects, both acute and delayed

Symptoms	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. Treat symptomatically.
---------------------------	---

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating and toxic gases and vapors. In the event of fire and/or explosion do not breathe fumes.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Evacuate personnel to safe areas. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak.
-----------------------------	---

Environmental precautions

Environmental precautions	Do not allow into any sewer, on the ground or into any body of water. Should not be released into the environment. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.
----------------------------------	--

Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
--------------------------------	---

Methods for cleaning up

Dike far ahead of liquid spill for later disposal. Soak up with inert absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. Prevent product from entering drains. Dam up. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling**Advice on safe handling**

Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation, especially in confined areas. In case of insufficient ventilation, wear suitable respiratory equipment. Use only with adequate ventilation and in closed systems. Avoid breathing vapors or mists. Always add acid to water.

Conditions for safe storage, including any incompatibilities**Storage Conditions**

Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers. Keep/store only in original container. Do not reuse container.

Incompatible materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents. Strong bases. Ammonia. Chlorinated compounds. Contact with metals may evolve flammable hydrogen gas. Metals.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters**Exposure Guidelines**

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Hydrochloric Acid 7647-01-0	Ceiling: 2 ppm	(vacated) Ceiling: 5 ppm (vacated) Ceiling: 7 mg/m ³ Ceiling: 5 ppm Ceiling: 7 mg/m ³	IDLH: 50 ppm Ceiling: 5 ppm Ceiling: 7 mg/m ³
Propargyl Alcohol 107-19-7	TWA: 1 ppm S*	(vacated) TWA: 1 ppm (vacated) TWA: 2 mg/m ³ (vacated) S*	TWA: 1 ppm TWA: 2 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information

Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls**Engineering Controls**

Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Tight sealing safety goggles. Face protection shield.

Skin and body protection

Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact.

Respiratory protection

If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene

Do not eat, drink or smoke when using this product. Avoid contact with skin, eyes or clothing. Avoid breathing (dust, vapor, mist, gas). Use personal protective equipment as required. Take off all contaminated clothing and wash it before reuse. Wash face, hands and any exposed skin thoroughly after handling.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Clear
Color	Blue
Odor	Acidic
Odor threshold	No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	<1	
Specific Gravity	Not Applicable	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	200 °F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	40mm Hg	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	9.16
VOC Content (%)	< 0.1%

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Exposure to air or moisture over prolonged periods.

Incompatible materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents. Strong bases. Ammonia. Chlorinated compounds. Contact with metals may evolve flammable hydrogen gas. Metals.

Hazardous Decomposition Products

Thermal decomposition can lead to release of irritating and toxic gases and vapors. Hydrogen chloride. Chlorine gas. Thermal decomposition can lead to release of toxic/corrosive gases and vapors. Hydrogen.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure****Product Information**

The primary effects and toxicity of this material are due to its corrosive nature.

Inhalation

Harmful if inhaled. Breathing of vapor can cause respiratory irritation and inflammation.

Breathing of mist or liquid can cause burns to the respiratory tract.

Eye contact Avoid contact with eyes. Corrosive to the eyes and may cause severe damage including blindness.

Skin Contact Avoid contact with skin. Corrosive. Contact with skin may cause severe irritation and burns.

Ingestion Ingestion causes acute irritation and burns to the mucous membranes of the mouth, trachea, esophagus and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrochloric Acid 7647-01-0	= 700 mg/kg (Rat)	> 5010 mg/kg (Rabbit)	= 1.68 mg/L (Rat) 1 h
Propargyl Alcohol 107-19-7	= 20 mg/kg (Rat)	= 16 mg/kg (Rabbit)	= 1200 ppm (Rat) 1 h = 1040 ppm (Rat) 1 h

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Corrosivity Causes burns. Extremely corrosive and destructive to tissue. Risk of serious damage to eyes.

Sensitization No Information available.

Germ cell mutagenicity No Information available.

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Hydrochloric Acid 7647-01-0	-	Group 3	-	X

IARC (International Agency for Research on Cancer)

Group 3 -Not classifiable as a human carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No Information available.

STOT - single exposure No Information available.

STOT - repeated exposure No Information available.

Chronic toxicity Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Avoid repeated exposure. Possible risk of irreversible effects.

Target organ effects EYES, Respiratory system, Skin.

Aspiration hazard No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral)	1,249.00
ATEmix (dermal)	26,328.21
ATEmix (inhalation-gas)	2,957.27
ATEmix (inhalation-dust/mist)	2.63

12. ECOLOGICAL INFORMATION

Ecotoxicity

0.11% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Hydrochloric Acid 7647-01-0	-	282: 96 h Gambusia affinis mg/L LC50 static	-
Nonylphenol Ethoxylate 9016-45-9	-	5: 96 h Fish mg/L LC50	-
Propargyl Alcohol	-	1.49 - 1.56: 96 h Pimephales	32: 24 h Daphnia magna mg/L

107-19-7		promelas mg/L LC50 flow-through	EC50
----------	--	---------------------------------	------

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods**Disposal of wastes**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

Chemical Name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Propargyl Alcohol 107-19-7	P102	-	-	-

Chemical Name	RCRA - Halogenated Organic Compounds	RCRA - P Series Wastes	RCRA - F Series Wastes	RCRA - K Series Wastes
Propargyl Alcohol 107-19-7	-	P102	-	-

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

UN/ID No.	Regulated UN1760
Proper shipping name	Corrosive liquids, n.o.s.
Hazard Class	8
Packing Group	II
Special Provisions	B2, IB2, T11, TP2, TP27
Description	UN1760, Corrosive liquids, n.o.s. (contains Hydrochloric Acid), 8, II
Emergency Response Guide Number	154

TDG

UN/ID No.	UN1760
Proper shipping name	Corrosive liquid, n.o.s.*
Hazard Class	8
Packing Group	II
Description	UN1760, Corrosive liquids, n.o.s. (Contains Hydrochloric Acid), 8, II

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
 DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
Hydrochloric Acid - 7647-01-0	1.0

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Hydrochloric Acid 7647-01-0	5000 lb	-	-	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Hydrochloric Acid 7647-01-0	5000 lb	5000 lb	RQ 5000 lb final RQ RQ 2270 kg final RQ
Propargyl Alcohol 107-19-7	1000 lb	-	RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations

California Proposition 65

WARNING: This product contains a chemical known to the state of California to cause cancer. WARNING: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Hydrochloric Acid 7647-01-0	X	X	X
Propargyl Alcohol 107-19-7	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 3	Flammability 0	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 3	Flammability 0	Physical hazards 0	Personal protection C

Issue Date 21-Apr-2017

Revision Date 20-Apr-2017

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the

date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet