



SAFETY DATA SHEET

Issue Date 10-Aug-2015

Revision Date 10-Aug-2015

Version 1

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name White-Lite Tile & Grout Whitener

Other means of identification

Product Code NL091

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1

Label elements

Emergency Overview

Danger

Hazard statements

Causes severe skin burns and eye damage



Appearance Clear

Physical state Liquid

Odor Rain Fresh

Precautionary Statements - Prevention

Do not breathe dust/fume/gas/mist/vapors/spray
 Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician

Specific Treatment (See Section 4 on the SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

Immediately call a POISON CENTER or doctor/physician

IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower

Wash contaminated clothing before reuse

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Immediately call a POISON CENTER or doctor/physician

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Drink plenty of water

Immediately call a POISON CENTER or doctor/physician

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other Information**

• Very toxic to aquatic life with long lasting effects

• Very toxic to aquatic life

Unknown Acute Toxicity

1E-05% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	Weight-%	Trade Secret
Sodium Hypochlorite	7681-52-9	1-5	*
Sodium Hydroxide	1310-73-2	1-5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures**General advice**

Immediate medical attention is required.

Skin Contact

Immediate medical attention is required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Eye contact

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area.

Inhalation

Remove to fresh air. Call a physician or poison control center immediately. If not breathing, give artificial respiration. If breathing is difficult, give oxygen.

Ingestion

Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Remove from exposure, lie down. Clean mouth with water and drink afterwards plenty of water. Call a physician or poison control center immediately.

Self-protection of the first aider

Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Most important symptoms and effects, both acute and delayed

Symptoms Any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating and toxic gases and vapors. In the event of fire and/or explosion do not breathe fumes.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment as required. Evacuate personnel to safe areas. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak.

Environmental precautions

Environmental precautions Do not allow into any sewer, on the ground or into any body of water. Should not be released into the environment. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Soak up with inert absorbent material. Clean contaminated surface thoroughly. Dike far ahead of liquid spill for later disposal. Take up mechanically, placing in appropriate containers for disposal. Prevent product from entering drains. Dam up. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Ensure adequate ventilation, especially in confined areas. Avoid contact with skin, eyes or clothing. In case of insufficient ventilation, wear suitable respiratory equipment. Use only with adequate ventilation and in closed systems.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of

children. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers.

Incompatible materials Incompatible with strong acids and bases. Incompatible with oxidizing agents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Sodium Hydroxide 1310-73-2	Ceiling: 2 mg/m ³	TWA: 2 mg/m ³ (vacated) Ceiling: 2 mg/m ³	IDLH: 10 mg/m ³ Ceiling: 2 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

- Eye/face protection** Tight sealing safety goggles. Face protection shield.
- Skin and body protection** Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact.
- Respiratory protection** If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene When using do not eat, drink or smoke. Wash contaminated clothing before reuse. Keep away from food, drink and animal feeding stuffs. Contaminated work clothing should not be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Avoid contact with skin, eyes or clothing. Take off all contaminated clothing and wash it before reuse. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state Liquid
Appearance Clear
Color Colorless
Odor Rain Fresh
Odor threshold No Information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	12.0 - 13.0	
Specific Gravity	1.086	
Viscosity	< 25 cP @ 25°C	
Melting point/freezing point	No Information available	
Flash point	None	
Boiling point / boiling range	212 °F	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	

Vapor density	No Information available
Water solubility	Complete
Partition coefficient	No Information available
Autoignition temperature	No Information available
Decomposition temperature	No Information available

Other Information

Density Lbs/Gal	9.05
VOC Content (%)	Not Applicable

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Exposure to air or moisture over prolonged periods.

Incompatible materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents.

Hazardous Decomposition Products

Thermal decomposition can lead to release of irritating and toxic gases and vapors.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Maybe harmful by inhalation, ingestion, in contact with eyes and skin,

Inhalation

Breathing of vapor can cause respiratory irritation and inflammation. Breathing of mist or liquid can cause burns to the respiratory tract.

Eye contact

Avoid contact with eyes. Corrosive to the eyes and may cause severe damage including blindness.

Skin Contact

Avoid contact with skin. Corrosive. Contact with skin may cause severe irritation and burns. Repeated exposure may cause skin dryness or cracking.

Ingestion

Do not taste or swallow. Ingestion causes acute irritation and burns to the mucous membranes of the mouth, trachea, esophagus and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Sodium Hypochlorite 7681-52-9	= 8200 mg/kg (Rat)	> 10000 mg/kg (Rabbit)	-
Sodium Hydroxide 1310-73-2	-	= 1350 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms

No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization

No Information available.

Germ cell mutagenicity

No Information available.

Carcinogenicity

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Sodium Hypochlorite 7681-52-9	-	Group 3	-	-

IARC (International Agency for Research on Cancer)

Group 3 -Not classifiable as a human carcinogen

Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Chronic toxicity	Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Avoid repeated exposure. Possible risk of irreversible effects.
Target organ effects	EYES, Respiratory system, Skin.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 1E-05% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (dermal) 58,506.00

12. ECOLOGICAL INFORMATION

This product contains a chemical which is listed as a marine pollutant according to DOT.

Ecotoxicity

0.41401% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Sodium Hypochlorite 7681-52-9	0.095: 24 h Skeletonema costatum mg/L EC50	0.28 - 1: 96 h Lepomis macrochirus mg/L LC50 flow-through 0.05 - 0.771: 96 h Oncorhynchus mykiss mg/L LC50 flow-through 4.5 - 7.6: 96 h Pimephales promelas mg/L LC50 static 0.06 - 0.11: 96 h Pimephales promelas mg/L LC50 flow-through 0.18 - 0.22: 96 h Oncorhynchus mykiss mg/L LC50 static 0.03 - 0.19: 96 h Oncorhynchus mykiss mg/L LC50 semi-static 0.4 - 0.8: 96 h Lepomis macrochirus mg/L LC50 static	2.1: 96 h Daphnia magna mg/L EC50 0.033 - 0.044: 48 h Daphnia magna mg/L EC50 Static
Sodium Hydroxide 1310-73-2	-	45.4: 96 h Oncorhynchus mykiss mg/L LC50 static	-
Sodium Sulfate 7757-82-6	-	13500: 96 h Lepomis macrochirus mg/L LC50 13500 - 14500: 96 h Pimephales promelas mg/L LC50 3040 - 4380: 96 h Lepomis macrochirus mg/L LC50 static 6800: 96 h Pimephales promelas mg/L LC50 static	630: 96 h Daphnia magna mg/L EC50 2564: 48 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation

No Information available.

Other adverse effects

No Information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not reuse container.

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status
Sodium Hydroxide 1310-73-2	Toxic Corrosive

14. TRANSPORT INFORMATION

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

UN/ID No.	UN1791
Proper shipping name	Hypochlorite solutions
Hazard Class	8
Packing Group	III
Special Provisions	IB3, N34, T4, TP2, TP24
Marine pollutant	This product contains a chemical which is listed as a marine pollutant according to DOT.
Description	UN1791, Hypochlorite solutions, 8, III
Emergency Response Guide Number	154

TDG

UN/ID No.	UN1791
Proper shipping name	Hypochlorite solutions
Hazard Class	8
Packing Group	III
Marine pollutant	This product contains a chemical which is listed as a marine pollutant according to TDG.
Description	UN1791, Hypochlorite solutions, 8, III

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Sodium Hypochlorite	100 lb	-	-	X

7681-52-9				
Sodium Hypochlorite 1310-73-2	1000 lb	-	-	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Sodium Hypochlorite 7681-52-9	100 lb	-	RQ 100 lb final RQ RQ 45.4 kg final RQ
Sodium Hydroxide 1310-73-2	1000 lb	-	RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Sodium Hypochlorite 7681-52-9	X	X	X
Sodium Hydroxide 1310-73-2	X	X	X
Sodium Sulfate 7757-82-6	-	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 3	Flammability 0	Instability 0	Physical and Chemical Properties Yes
HMIS	Health hazards 3	Flammability 0	Physical hazards 0	Personal protection C

Issue Date 10-Aug-2015

Revision Date 10-Aug-2015

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet