



# VMH500

WHOLE ROOM  
METAL HEATER



## About the VMH500

Our new family of steel heaters includes the VMH500, offering enhanced performance and control plus serious comfort and efficiency — all while complementing your style. With a cool-touch, powder-coated metal case, two LED displays for cross-room viewing, a remote control, discreet cord storage, auto-climate control and our signature Whole Room Vortex Heat Circulation, it not only elevates the look and feel of the typical home heater, it does its job remarkably well. A metal inlet grill that keeps dust (and fingers) at bay, plus other safety features, ensures cozy comfort with peace of mind, along with a 5-year satisfaction guarantee.

## Featuring

- WHOLE ROOM HEAT CIRCULATION
- POWDER-COATED STEEL CONSTRUCTION
- AUTO-CLIMATE CONTROL
- TIPOVER PROTECTION
- 2-STAGE AUTO SHUTOFF
- COOL-TOUCH STEEL CASE
- REMOTE CONTROL
- 2 HEAT SETTINGS (LOW/HIGH/FAN ONLY): 750 AND 1,500 WATTS
- CORD STORAGE COMPARTMENT
- INTEGRATED HANDLE
- DUST-REDUCING METAL INLET GRILL
- 5-YEAR SATISFACTION GUARANTEE

## Specs

<b>Item Number</b> EH1-0116-69	<b>Country of Origin</b> China	<b>Carton Cube (cu. ft.)</b> 0.94	<b>Case Cube (cu. ft.)</b> 2.15
<b>Color</b> Metallic champagne	<b>Unit Dimensions (est.)</b> 9.20" L x 9.38" W x 11.67" H	<b>Case Dimensions (est.)</b> 22.05" L x 11.42" W x 14.76" H	<b>40" x 48" GMA Pallet Qty.</b> TBD
<b>Unit UPC</b> 043765010358	<b>Carton Dimensions (est.)</b> 11" L x 10.75" W x 13.8" H	<b>Case Weight</b> TBD	<b>40' Container Qty. (est.)</b> 2,004
<b>SCC 14</b> 10043765010355	<b>Carton Weight</b> TBD	<b>Case Quantity</b> 2	<b>40' HC Container Qty. (est.)</b> 2,338



INTEGRATED HANDLE AND CONTROLS



DUST-REDUCING METAL INLET GRILL



REMOTE CONTROL



COMPLEMENTARY STYLE



Designed and engineered in USA. Manufactured in China. This product has earned the ETL Listing mark. © 2016 Vornado Air, LLC. Andover, Kansas 67002 USA. Specifications subject to change without notice. Patent pending.

1.800.234.0604  
VORNADO.COM