



SAFETY DATA SHEET

Issue Date 21-Feb-2017

Revision Date 21-Feb-2017

Version 3

1. PRODUCT AND COMPANY IDENTIFICATION

Product identifier

Product Name Clean Freeze Freezer Cleaner

Other means of identification

Product Code NL849

Synonyms None

Details of the supplier of the safety data sheet

Company Name Nyco Products Company
5332 Dansher Road
Countryside, IL 60525
(708) 579-8100
nycoproducts.com

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Oral	Not classified
Acute toxicity - Dermal	Not classified
Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 1

Label elements

Emergency Overview

Danger

Hazard statements

Causes skin irritation

Causes serious eye damage



Appearance Clear

Physical state Liquid

Odor Typical

Precautionary Statements - Prevention

Wash face, hands and any exposed skin thoroughly after handling
Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Specific Treatment (See Section 4 on the SDS)
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
Immediately call a POISON CENTER or doctor/physician
IF ON SKIN: Wash with plenty of soap and water
If skin irritation occurs: Get medical advice/attention
Take off contaminated clothing and wash before reuse

Precautionary Statements - Disposal

Disposal should be in accordance with applicable regional, national and local laws and regulations

Hazards not otherwise classified (HNOC)**Other Information**

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES**First aid measures**

Skin Contact	Wash off immediately with plenty of water. Wash skin with soap and water.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a physician.
Inhalation	Remove to fresh air.
Ingestion	Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects, both acute and delayed

Symptoms	Any additional important symptoms and effects are described in Section 11: Toxicology Information.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES**Suitable extinguishing media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No Information available.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Monoethanolamine 141-43-5	STEL: 6 ppm TWA: 3 ppm	TWA: 3 ppm TWA: 6 mg/m ³ (vacated) TWA: 3 ppm (vacated) TWA: 8 mg/m ³ (vacated) STEL: 6 ppm (vacated) STEL: 15 mg/m ³	IDLH: 30 ppm TWA: 3 ppm TWA: 8 mg/m ³ STEL: 6 ppm STEL: 15 mg/m ³
Diethanolamine 111-42-2	TWA: 1 mg/m ³ inhalable fraction and vapor S*	(vacated) TWA: 3 ppm (vacated) TWA: 15 mg/m ³	TWA: 3 ppm TWA: 15 mg/m ³

NIOSH IDLH *Immediately Dangerous to Life or Health*

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers, Eyewash stations & Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Clear
Color	Yellow
Odor	Typical
Odor threshold	No Information available

Property	Values	Remarks • Method
pH	10.5 - 11.5	
Specific Gravity	1.023	
Viscosity	Water Thin	
Melting point/freezing point	-40 °C / -40 Degrees	
Flash point	Above 200°F	
Boiling point / boiling range	>= 100 °C / 212 ° F (at 760 mm Hg) Degrees	
Evaporation rate	No Information available	
Flammability (solid, gas)	No data available	
Flammability Limits in Air		
Upper flammability limit:	No Information available	
Lower flammability limit:	No Information available	
Vapor pressure	No Information available	
Vapor density	No Information available	
Water solubility	Complete	
Partition coefficient	No Information available	
Autoignition temperature	No Information available	
Decomposition temperature	No Information available	

Other Information

Density Lbs/Gal	8.54
VOC Content (%)	60

10. STABILITY AND REACTIVITY

Reactivity
No data available

Chemical stability
Stable under recommended storage conditions.

Possibility of Hazardous Reactions
None under normal processing.

Conditions to avoid
Extremes of temperature and direct sunlight.

Incompatible materials
None known based on information supplied.

Hazardous Decomposition Products
None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Avoid breathing vapors or mists. Inhalation of vapors in high concentration may cause irritation of respiratory system.
Eye contact	Avoid contact with eyes. Corrosive. Causes serious eye damage.
Skin Contact	Avoid contact with skin. Causes skin irritation.
Ingestion	Do not taste or swallow. May cause gastro intestinal irritation.

Information on toxicological effects

Symptoms No Information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization	No Information available.
Germ cell mutagenicity	No Information available.
Carcinogenicity	No Information available.
Reproductive toxicity	No Information available.
STOT - single exposure	No Information available.
STOT - repeated exposure	No Information available.
Target organ effects	Central nervous system, EYES, Respiratory system, Skin.
Aspiration hazard	No Information available.

Numerical measures of toxicity - Product Information

Unknown Acute Toxicity 0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral)	10,371.00 mg/kg
ATEmix (dermal)	13,953.00 mg/kg
ATEmix (inhalation-dust/mist)	30.20 mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

3% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
Propylene Glycol 57-55-6	19000: 96 h Pseudokirchneriella subcapitata mg/L EC50	41 - 47: 96 h Oncorhynchus mykiss mL/L LC50 static 51600: 96 h Oncorhynchus mykiss mg/L LC50 static 51400: 96 h Pimephales promelas mg/L LC50 static 710: 96 h Pimephales promelas mg/L LC50	1000: 48 h Daphnia magna mg/L EC50 Static 10000: 24 h Daphnia magna mg/L EC50
Monoethanolamine 141-43-5	15: 72 h Desmodesmus subspicatus mg/L EC50	227: 96 h Pimephales promelas mg/L LC50 flow-through 3684: 96 h Brachydanio rerio mg/L LC50 static 300 - 1000: 96 h Lepomis macrochirus mg/L LC50 static 114 - 196: 96 h Oncorhynchus mykiss mg/L LC50 static 200: 96 h Oncorhynchus mykiss mg/L LC50 flow-through	65: 48 h Daphnia magna mg/L EC50
Diethanolamine 111-42-2	2.1 - 2.3: 96 h Pseudokirchneriella subcapitata mg/L EC50 7.8: 72 h Desmodesmus subspicatus mg/L EC50	4460 - 4980: 96 h Pimephales promelas mg/L LC50 flow-through 1200 - 1580: 96 h Pimephales promelas mg/L LC50 static 600 - 1000: 96 h Lepomis macrochirus mg/L LC50 static	55: 48 h Daphnia magna mg/L EC50

Persistence and degradability

No Information available.

Bioaccumulation

Bioaccumulative potential.

Other adverse effects No Information available**13. DISPOSAL CONSIDERATIONS****Waste treatment methods****Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.**Contaminated packaging** Do not reuse container.**14. TRANSPORT INFORMATION**

The basic description below is specific to the container size. This information is provided for at a glance DOT information. Please refer to the container and/or shipping papers for the appropriate shipping description before tendering this material for shipment. For additional information, please contact the distributor listed in section 1 of this SDS.

DOT

UN/ID No.	UN1760
Proper shipping name	Corrosive liquids, n.o.s.
Hazard Class	8
Packing Group	III
Special Provisions	IB3, T7, TP1, TP28
Description	UN1760, Corrosive liquids, n.o.s (contains Ethanolamine), 8, III
Emergency Response Guide Number	154

TDG

UN/ID No.	UN1760
Proper shipping name	Corrosive liquids, n.o.s.
Hazard Class	8
Packing Group	III
Description	UN1760, Corrosive liquids, n.o.s (contains Ethanolamine), 8, III

15. REGULATORY INFORMATION**International Inventories**

TSCA	Complies
DSL/NDSL	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	No
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product contains Prop 65 chemicals.

Chemical Name	California Proposition 65
Diethanolamine - 111-42-2	Carcinogen

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Propylene Glycol 57-55-6	X	-	X
Monoethanolamine 141-43-5	X	X	X
Diethanolamine 111-42-2	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards 2	Flammability 0	Instability 0	Physical and Chemical Properties Yes Personal protection B
HMIS	Health hazards 2	Flammability 0	Physical hazards 0	

Issue Date 21-Feb-2017

Revision Date 21-Feb-2017

Revision Note

No Information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet