

# DRUM & PAIL HEATERS

Featuring patented technology, **Powerblanket® Lite** delivers a barrier of uniform directional heat where it's needed most – preventing fluids from freezing and maintaining optimal temperatures. This innovative heat spreading technology insulates, protects and maintains heat in a wide variety of applications. Use our innovative Powerblanket Lite drum/barrel and pail heaters to protect your product from freezing and heat to optimal viscosity.

**powerblanket**  
*lite*



## STANDOUT FEATURES:

- Quickly heat materials to a preset 125° F / 51.7° C (± 10° F/5° C)
- Provide an insulated full-wrap design
- Deliver uniform heat to temperature sensitive products
- Preserve expensive materials without scorching or burning
- Prevent waste by maintaining consistent temperatures
- Certified to UL/CSA/CE standards





## MAINTENANCE-FREE HEATING

Powerblanket Lite products provide a maintenance free heating solution, which eliminates the headache of maintaining critical temperatures. If stored properly, chemicals and industrial products will last longer and be more effective. In turn, this saves time, hassle, and money.

On those occasions when you don't need all the extra strength and durability, however, there's no use paying for more than you need, right? That's why we created our Powerblanket Lite line. For those jobs that don't necessitate the most robust and sturdy application possible, the Powerblanket Lite line is the best answer.



CERTIFIED TO UL/CSA/CE STANDARDS  
CONFORMS TO ANSI/UL STD 499  
CERTIFIED TO CAN/CSA C22.2 NO 130  
CID2-T4 FOR HAZARDOUS LOCATIONS AVAILABLE

## POWERBLANKET LITE TECHNICAL SPECS

Product Category	Model #	Temperature Control	Approx. Product Temperature	Container Dimensions (inch/cm)	Voltage	Wattage (+-5%)	Amps (+-5%)	Weight
5 GALLON / 19 LITER BUCKET	PBL05	Internal Preset	125° F ±10°F/51.7° C ± 5° C	11.8"D x 15.6"H / 30cmx40cm	120V	120	1.00	1.5
15 GALLON /57 LITER BUCKET	PBL15	Internal Preset	125° F ±10°F/51.7° C ± 5° C	14.4"D x 26.3"H / 37cmx67cm	120V	180	1.50	2.8
30 GALLON / 114 LITER DRUM	PBL30	Internal Preset	125° F ±10°F/51.7° C ± 5° C	12.5"Dx24"H / 32cmx61cm	120V	280	2.33	4.1
55 GALLON / 208 LITER DRUM	PBL55	Internal Preset	125° F ±10°F/51.7° C ± 5° C	23.3"D x 34.9"H / 59cmx89cm	120V	240	2.00	3.1
55 GALLON / 208 LITER DRUM	PBL55F	Internal Preset	125° F ±10°F/51.7° C ± 5° C	23.3"D x 34.9"H / 59cmx89cm	120V	400	3.33	10.1
1 GALLON/4 LITER PAIL	PBL1G	Internal Preset	84° ± 10° F / 29°C ± 5° C	6.5"D x 7.5"H / 17cmx19cm	120V	45	0.38	0.6
2 GALLON/8 LITER PAIL	PBL2G	Internal Preset	84° ± 10° F / 29°C ± 5° C	9.2"D x 9.5" H / 23cmx24cm	120V	45	0.38	0.8

All Standard AC Products are Certified by ETL to Applicable ANSI/UL/CSA & CE Safety Standards --- cETLus & C E

Additional specifications available including: 240 VAC and Class I Division 2 Groups A through D ; T4

Powerblanket reserves the right to improve products and change specifications without notification \*All temperatures may vary based on boundary conditioner that fits your specific needs.