# **Exterior**

# ACCESS DOOR

The Babcock-Davis Exterior Access Door provides efficient access from the exterior of your building without compromising security or weather resistance.

# **FEATURES**

COMPATIBLE WITH BUILDING KEY With the mortise lock prep option, you can match the mortise cylinder to that of your building's other access points.

**TEMPERATURE CONTROL** With 1.6 inch polyurethane insulation, the Babcock-Davis Exterior Door is constructed to protect your building from the harshest climates.

AIR + WATER PENETRATION TEST Independent lab testing for air leakage per ASTM E 283 and water leakage per ASTM E 331-00 assures the best protection against the elements.



## **DETAILS**

DOOR 24 gage Steel

FRAME 0.080 inch 6063-T5 Extruded Aluminum

- Min: 12 inches by 12 inches
- Max: 48 inches by 60 inches

INSTALLATION Ceiling or Wall

**FLANGE** Exposed or Plaster/Stucco Bead

**HINGE** Stainless Steel Continuous Piano

- Door: Paint Grip Finish
- Frame: Mill

**INSULATION** 1.6 inch Polyurethane; R-11

**GASKETING** EPDM Self-Adhesive, Continuous

### **FLANGES**







Plaster/Stucco Bead

# **LATCHES**



Non-Locking Handle



Screwdriver Cam Latch



Locking Handle



Mortise Lock Prep

# **ORDER GUIDE**

BASE	FLANGE	LATCH	WIDTH	Х	LENGTH	OPTIONS
вх				x		
	T 1 inch Flange	A Non-Locking Handle	Standard Sizes (W x L)			A Aluminum Door
	P Plaster/Stucco bead	C Screwdriver Cam Latch	12" x 12" 20" 16" x 16" 24"	20" x 30	" 36" x 36"	C Drip Cap
		L Locking Handle		24" x 30		<b>G</b> Galvanized Door
		M Mortise Lock (1-1/8") Prep				M Masonry Anchors
		P Padlock Hasp				P Padlock Hasp
						S Type 304 Stainless Steel

Rough opening is door size. Additional sizes available, call for more information.