THINK INSIDE THE BOX

The Powerblanket® Hot Box saves you money by keeping your products from freezing without the risk of overheating. For example, Vern Fiehler, of Quick Road Repair in Alaska, saved money by keeping his product from burning up, which is what happened with his old method. He met with the field maintenance crew of the Juneau Alaska International Airport to demonstrate his product called Instant Road Repair (IRR). For his demonstration, he needed to bring the IRR up to working temperature, and used a forced air ceramic heater to do so. Unfortunately, during the presentation, the product was not performing well. To his surprise, Vern discovered that the product overheated 40°F / 22°C past its maximum temperature. That cost him a pallet of product and embarrassed him. Since then, Vern has used the Powerblanket® Hot Box.





POWERBLANKET BULK MATERIAL WARMERS (HOT BOX) ARE PERFECT FOR COLD WEATHER STORAGE

- Preserve expensive materials without overheating or burning
- Peace of mind that materials are safely maintained at consistent temperatures
- Energy efficient design saves on operating costs
- Flexibility to adjust temperature (PRO model only)

The Hot Box pallet warmer can be easily assembled, disassembled, and reassembled. This makes it ideal for cold weather storage, freeze protection, transporting, job site heating, remote location use, and other heating requirements. Standard Hot Boxes hold product between 100°F and 120°F and optional adjustable thermostatic controllers allow temperatures to be precisely controlled.



CERTIFIED TO UL/CSA/CE STANDARDS CONFORMS TO ANSI/UL STD 499 CERTIFIED TO CAN/CSA C22.2 NO 130 CID2-T4 FOR HAZARDOUS LOCATIONS AVAILABLE

AVAILABLE IN THREE PERFORMANCE LEVELS:

	COX-IBLERIA	Powerblankst			
Powerblanket Lite Hot Box	The Powerblanket Hot Box	The Premium Hot Box			
 2 sizes available: Fits 40"x48" or 36"x48" pallets 800 Watt design Preserves temperature sensitive material Quick and easy assembly for portability and storage Great solution for palletized products: paint, caulk, resins and epoxies, etc. Two side access doors on opposite sides Certified to UL/CSA/CE standards 	 Offers all the features of the Powerblanket Lite Hot Box, plus: A durable, vinyl shell Higher wattage (1200 Watts) for faster heating times & more extreme 	 Offers all the features of the Powerblanket Hot Box, plus: A larger footprint (Fits 48" x 48" pallet) An internal steel frame The highest wattage (1440 Watts) A controller for precise temperature regulation 			

Part Number	Product Line	Dimensions	Power	Approx Temp Range	Voltage	Vinyl	Frame	Cord	Control
PBLHB48-800	Powerblanket Lite	36" x 48"	800 Watts	100° F - 110° F	110V	D12	Plastic Frame	6 ft	Internal Thermostat
PBLHB54-800	Powerblanket Lite	40"x48"	800 Watts	100° F - 110° F	110V	D12	Plastic Frame	6 ft	Internal Thermostat
HB48-1200	Powerblanket	36"x48"	1200 Watts	100° F - 110° F	110V	D15	Plastic Frame	6 ft	Internal Thermostat
HB54-1200	Powerblanket	40"x48"	1200 Watts	100° F - 110° F	110V	D15	Plastic Frame	6 ft	Internal Thermostat
HB64PRO-1440	Powerblanket	48"x48"	1440 Watts	100° F - 120° F	110V	D15	Steel Frame	6 ft	Controller