

## MSDBF

### Manual Sidedrive Dual Mast Flap Folder

The BestPack™ MSDBF sealer is a unique multi-purpose machine. Featuring a convenient top 3-flap folder and bottom T-rail leading to an extended side-drive system, the MSDBF enables a person to efficiently erect, pack, flap fold, and seal a carton in one station. Dual telescopic masts allow for an extra 4" carton height extension on the upper assembly and two 110V UL-approved electric motors power the extended side belt drive.

Our MSDBF line incorporates our exclusive 2" or 3" pop-out pressure-sensitive "High Speed" tape heads with BestPack's patented tab adjustment. All BestPack units are available in our standard baked enamel finish and food grade 304 stainless steel.



## Key Points of the Carton Sealer



Operator Fed



Uniform Cartons



Top & Bottom Seal

## Features

- Designed for Uniform Applications Capable of Interchanging: 2" or 3" Tape Heads
- Extended Two Side Belts
- Bottom 4 Flap Folder w/Top 3 Flap Folder
- Telescopic Mast Design
- Attached T-Rail Packing Station (additional T-Rail adaptors may be needed depending on box sizes)
- Extra 4" Carton Height Adjustment Available on Upper Assembly
- Adjustable Bed Height 23.5" to 30.0"
- Width/Height Adjustment either side of Carton Sealer
- Exclusive 4 Roller Upper Side Compression Unit
- Tape Roll Lengths: 1000 yd., 1500 yd., 2000 yd.
- Heavy Duty Frame

- UL Approved Electrical Parts
- Electrical on/off box can be mounted on either side of machine

## Options

- Spare Parts Kit
- T-Rail Adaptors (needed depending on carton sizes)
- Motorized Height and/or Width Adjustment
- Exit Conveyor
- Locking Casters w/Support Brackets
- Interlock Safety Gates
- Stainless Steel

# Extra Accessories to Improve Efficiency



Spare Parts Kit



Locking Casters  
w/Support Brackets



Exit Conveyor



Spare Tape Head

- High Speed Motor Upgrade (Up to 125 ft. per min.)
- Stainless Steel
- Carton Sealing Tape

## Machine & Carton Specifications

**110 Volts 60 Hz**  
Power Requirements

**Up to 15 Cartons/min.**  
Speed

**No Line**  
Air Requirements

**420-648 lbs**  
Shipping Weight

Model	Machine Dimensions Length x Width x Height	Carton Range* Length (min. - max.) x Width (min. - max.) x Height (min. - max.)	Conveyor Height Adjustment Height (min. - max.)	Cartons per min.	Shipping Weight (lbs.)
MSDBF22-2 <b>2" Tape Head</b>	(99.6") x (32.8") x (70.3")	(7.8" - 23.6") x (7.8" - 19.6") x (4.0" - 19.6")	(23.5" - 30.0")	Up to 15	420
MSDBF22-3 <b>3" Tape Head</b>	(99.6") x (32.8") x (70.3")	(7.8" - 23.6") x (7.8" - 19.6") x (4.0" - 19.6")	(23.5" - 30.0")	Up to 15	420
MSDBF32-2 <b>2" Tape Head</b>	(125.0") x (43.8") x (70.3")	(14.0" - 48.0") x (12.0" - 30.0") x (6.0" - 19.6")	(23.5" - 30.0")	Up to 15	648
MSDBF32-3 <b>3" Tape Head</b>	(125.0") x (43.8") x (70.3")	(14.0" - 48.0") x (12.0" - 30.0") x (6.0" - 19.6")	(25.8" - 30.0")	Up to 15	648

Information subject to change without notice.

\*Outside Dimensions Only  
All specifications capable of customization.