

6030

IP67 Portion Control Scale



- **Accuracy**— +/- 3 divisions
- **Capacity**— 5000 g x 1 g, 10 lb x 0.002 lb, 10 lb x 0.05 oz, 160 oz x 0.05 oz
- **Units**— g, lb, oz, lb:oz
- **Display**— 20 mm / 0.8" LCD with five digits
- **Construction**— Food grade stainless steel upper cover and removable stainless steel platter for easy cleaning
- **Battery or AC/DC Operation**— 9 volt alkaline battery (included), AC adapter (not included)
- **Three Function Keys**— On/off, tare/zero, units
- **Low Battery/Overload Indication**
- **Power Saving with Auto Off Feature**

VALUE IN
WEIGHING

6030 IP67 Portion Control Scale

Specifications

Capacity: 5000 g x 1 g, 10 lb x 0.002 lb, 10 lb x 0.05 oz,
160 oz x 0.05 oz

Display: LCD

Keyboard: On/off, tare/zero, units

Unit: kg, g, lb, lb/oz, oz

Power: AC and 9V battery

Options:

1148-15322: 9 VDC adapter

Battery Life: 20 hours continuous use

Operating Temperature: 5° C - 35° C / 41° F - 95° F

Specifications

Platform Dimension:

150 mm (W) x 120 mm (L) / 5.9" W x 4.7" L

Product Dimension:

170 mm (W) x 150 mm (L) x 40 mm (H)

6.6" W x 5.9" L x 2" H

Product Weight: 0.6 kg / 1.5 lb

Packaging Dimension:

254 mm (W) x 196 mm (L) x 76 mm (H)

10" W x 7.75" L x 3" H

Shipping Weight: 1 kg / 2 lb

Part Number: 816965006557



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

