

8035

COMPACT SLIDE TOP UTILITY CART



- Locking slide top design gives added work space
- 5" x 2" heavy-duty casters (2 locking)
- Heavy-duty 18 gauge (1.2mm) steel frame
- Compact and easy to maneuver
- Full extension roller bearing drawer slides
- Durable grooved rubber mats on the slide top
- EVA foam drawer liners to keep tools in place during transport
- Durable powder coat finish

SPECIFICATIONS

Capacity..... 450 lbs.
 Material 18 Gauge Steel
 Width 29"
 Depth 20.5"
 Height 39.3"
 Top Bin Height 5"
 Top and Bottom
 Drawer Height 3"
 Bottom Shelf Height 3"
 Weight 114.64 lbs.

ACCESSORIES

EVA Foam Tray Liner 1110
 EVA Foam Drawer Liner.....1111



BLACK
8035



RED
8035R

8019

HEAVY DUTY ADJUSTABLE WORK TABLE WITH DRAWER



- Easy to maneuver 2" casters
- 1" deep drawer for convenient storage
- On board screwdriver and pry bar holder
- Air tool hose cut outs for easy and quick storage
- Durable textured rubber mat for non-skid surface
- Adjustable table height to work on a variety of different vehicles
- Durable powder coat finish

SPECIFICATIONS

Capacity..... 220 lbs.
 Maximum Height 47.8"
 Minimum Height 34"
 Tray Dimensions 29" x 20" x 1"
 Weight 40.8 lbs.

