

Chem-Crest[®] 211

*Phosphate- and caustic-free, heavy-duty,
ultrasonic liquid detergent concentrate*



Description

Chem-Crest 211 is a multipurpose, heavy-duty, phosphate- and caustic-free alkaline liquid cleaner. It is useful in many applications demanding removal of various contaminants such as oils, greases, and particulate. This detergent finds many uses throughout industrial, mechanical, and maintenance cleaning operations. Chem-Crest 211 is freely water soluble and inhibited to help prevent flash rusting.

Substrate Compatibility

Chem-Crest 211 is safe on various metals, including aluminum, brass, bronze, copper, and steels, glass, plastics, hard rubber articles, and ceramics, when used as directed.

Physical Data

Flash Point: None

Specific Gravity: 1.08

pH: 5% solution = 11.4 +/- 0.5

Solubility in Water: Complete

Volatiles: N/A

**These are typical values and do not constitute specifications.

Storage Conditions and Disposal Methods

Avoid freezing conditions. Dispose in accordance with Federal, State, and Local regulations and procedures. No products contained in this concentrate are regulated under SARA Title III, Section 313.

Safety Precautions

See Material Safety Data Sheet

Operating Conditions

Chem-Crest 211 is typically used at 3 - 10% by volume in ultrasonic applications. Normal operating temperatures: 120 - 180°F, dependent on the material makeup of the substrate, and the contaminants being removed. Contact your Crest representative for product-line specific recommendations. Recommended rinsing water temperature: 120 - 150°F.

Typical Contaminants Removed

Chem-Crest 211 removes heavy oils, greases, tripoli, ceramic dust, lubricants, buffing and lapping compounds, fingerprints, airborne contaminants, light silicone oils and ink markings.

Availability

Chem-Crest 211 is available in cases of (4) x 1-gallon plastic bottles, 5-gallon pails, 55-gallon containers, and custom bulk sizes.

For further information on this product, please contact the Chemical Sales Office at:

Crest Ultrasonics Corp.

Scotch Road at Trenton Mercer Airport

P.O. Box 7266

Trenton, NJ 08628

P: (609) 883-4000

F: (609) 406-7006

labtech@crest-ultrasonics.com

Crest Ultrasonics maintains sales offices in the United States, Malaysia, Singapore, Japan, Germany, the United Kingdom, India, and France.

Our chemicals are blended at our Philadelphia, PA office, Custom Blends, Inc. – A Division of Crest Ultrasonics.

Disclaimer: All statements, technical information and recommendation contained herein are based on tests or other information available to us which we believe to be reliable, but the accuracy or completeness thereof is not guaranteed and are made without representation or warranty. They are presented for your own investigation and verification. Products discussed are sold without warranty, expressed or implied, in law or fact and upon the condition that purchasers make their own tests to determine the suitability of such products to their particular purpose. We shall not be liable for any injury, loss or damage direct or consequential, arising out of use or the inability to use the product. It is the user's obligation and responsibility to determine that any use of the product or the information may infringe on patent rights.