

20 GALLON PARTS WASHER

Product Features:



Washing Basket For
Cleaning of Smaller Parts



Fusible Linked Lid Arm
Prevents Accidental Injuries
In Case Of Fire



Electronic ON/OFF Switch
Controls Pump Operation



Flexible Spray Nozzle



Bottom Storage Shelf for
Extra Space



1 YEAR
LIMITED WARRANTY

20 GALLON PARTS WASHER

- Fusible Linked Lid Arm To Prevent Accidental Injury In Case Of Fire
- 3.2 mil Epoxy-Polyester Powder Coat Paint Finish
- Includes Parts Basket for Cleaning Smaller Parts
- Large One Piece Tank for Cleaning Big Parts
- Solid Steel Design That Won't Leak
- Removable Work Surface Tray
- 3.95 GPM Max Flow Rate
- Electric Pump Included
- Pump ON/OFF Switch
- Flexible Nozzle

Product Specifications:

PARTS WASHER	WIDTH	DEPTH	HEIGHT	CAPACITY
Solvent Tank	28"	19"	10 1/4"	3.15 cu ft
Parts Basket	9 1/2"	6"	3 1/2"	0.12 cu ft
Storage Shelf	26 1/4"	17"	13"	3.36 cu ft

METAL THICKNESS

Frame	1.0 mm
Legs	1.5 mm

MAXIMUM CAPACITIES

Tank	110 lbs
Drying Shelf	110 lbs
Recovery Bin	110 lbs
Storage Shelf	110 lbs



MODEL No.	PRODUCT DESCRIPTION	WIDTH	DEPTH	HEIGHT	PC WT	SHIPWT	UPC CODE
RD00820310	20 Gallon Parts Washer	30"	21 1/4"	34 5/8"	51 lbs.	58 lbs.	034518 01008 4