

RS Series

Random Sidedrive

The BestPack RS Series is a Semi-Automatic Random Tape Carton Sealer built for speed and rugged dependability. Using side belt drives, the RS easily seals a wide range of random carton weights and sizes, with masts that allow for an extra 4" of carton height on the upper assembly. Able to effectively seal very light to very heavy cartons, BestPack's RS sealer is a workhorse and the most flexible unit in our random carton sealer product line.

Our RS line incorporates our exclusive 2" or 3" pop-out pressure-sensitive "High Speed" tape heads with BestPack's patented tab adjustment. All BestPack units are available in our standard baked enamel finish and food grade 304 stainless steel for 21 CFR 110 compliance.



Key Points of the Carton Sealer



Operator Fed



Random Cartons



Top & Bottom Seal

Features

- Handles Random Carton Sizes
- Adjustable Bed Height from RS22, RS23, & RS32: 20.5" - 30"
RS33: 20.5" - 30"
- 2 Side Belt Driven
- Extra 4" Carton Height Adjustment Available on Upper Assembly
- Tape Roll Lengths: 1,000 yd., 1,500 yd., 2,000 yd.
- Heavy Duty Frame
- UL Approved Electrical Parts
- Capable of Interchanging 2" or 3" Tape Heads
- Electrical On/Off Box can be Mounted on Either Side of the Carton Sealer
- Exclusive Pop-out Pressure Sensitive "High Speed" Tape Head with Patented Tab Adjustment and Noise Reduction Arm

Options

- Spare Parts Kit
- High Speed Motor Upgrade (Up to 125 ft. per min.)
- Locking Heavy-Duty Casters
- Interlock Safety Gates
- Low Tape or No Tape Sensor
- Infeed/Exit Conveyor w/L-Bracket Stabilizer
- Food Grade 304 Stainless Steel

Extra Accessories to Improve Efficiency



Spare Parts Kit



Locking Casters



Long Infeed/Exit Conveyor
w/ L-Bracket Stabilizer



Spare Tape Head

- High Speed Motor Upgrade (Up to 125 ft. per min.)
- High Speed Belt Drive (Up to 150 ft. per min. - Requires High Speed Motor and High Speed Belt Drives)
- Carton Sealing Tape

Machine & Carton Specifications

110 Volts 60 Hz
Power Requirements

Up to 15 Cartons/min.
Speed

55-80 PSI
5 SCFM
Air Requirements

410-600 lbs
Shipping Weight

Model	Machine Dimensions Length x Width x Height	Carton Range* Length (min. - max.) x Width (min. - max.) x Height (min. - max.)	Conveyor Height Adjustment Height (min. - max.)	Cartons per min.	Shipping Weight (lbs.)
RS22-2 2" Tape Head	(42.9") x (34.8") x (71.8")	(6.0" - U) x (4.25" - 20.0") x (4.0" - 21.0")	(20.5" - 30.0")	Up to 15	410
RS22-3 3" Tape Head	(42.9") x (34.8") x (71.8")	(6.0" - U) x (5.25" - 21.0") x (4.0" - 21.0")	(20.5" - 30.0")	Up to 15	410
RS23-2 2" Tape Head	(42.9") x (34.8") x (76.0")	(6.0" - U) x (4.5" - 20.0") x (4.0" - 30.0")	(20.5" - 30.0")	Up to 12	440
RS23-3 3" Tape Head	(42.9") x (34.8") x (76.0")	(6.0" - U) x (5.5" - 21.0") x (4.0" - 30.0")	(20.5" - 30.0")	Up to 12	440
RS32-2 2" Tape Head	(42.9") x (44.2") x (71.8")	(6.0" - U) x (4.5" - 30.0") x (4.0" - 20.5")	(20.5" - 30.0")	Up to 12	462
RS32-3 3" Tape Head	(42.9") x (44.2") x (71.8")	(6.0" - U) x (5.5" - 30.0") x (4.0" - 20.5")	(20.5" - 30.0")	Up to 12	462
RS33-3 3" Tape Head	(42.9") x (44.2") x (76.0")	(6.0" - U) x (5.5" - 30.0") x (4.0" - 30.0")	(20.5" - 30.0")	Up to 12	600

Information subject to change without notice.

* Outside Dimensions Only
U - Unlimited
High Speed Option Available

BestPack™

the total tape sealing solution
Information subject to change without notice.

For more information please go to:
www.bestpack.com or call us at **1.888.588.2378**

All contents are Copyright © 2017 BestPack Packaging Systems. All rights reserved. This document is BestPack Public Information.