

Model 40XL2

In-Line Single Check Valve

Application

Ideal for use where Lead-Free* valves are required. Designed for installation on potable domestic and commercial water systems such as well pump systems and applications requiring tight seating. For use as a positive backstop to eliminate reduced pressure principle backflow preventer discharge caused by pressure fluctuations or water hammer.

Standards Compliance

 UL® Classified - ANSI/NSF Standard 61, Annex G* (*0.25% maximum weighted average lead content)



Main valve body Lead Free Brass Poppet Polyetherimide

Seat NBR

Spring Stainless Steel, 300 series

Features

Sizes: 1/2", 3/4", 1", 1 1/4", 1 1/2", 2"

Maximum working water pressure 400 WOG
Maximum working water temperature 210°F
End connections Threaded ANSI B1.20.1








Dimensions & Weights (do not include pkg.)

MODEL SIZE		DIMENSIONS (approximate)						WEIGHT	
		Α		В		С		WEIGHT	
in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kg
1/2	15	2 5/15	59	1	25	1 3/8	35	0.3	0.1
3/4	20	2 9/16	65	1 1/4	32	1 11/16	43	0.5	0.2
1	25	2 3/4	70	1 1/2	38	1 15/16	49	0.7	0.3
1 1/4	32	2 15/16	75	1 7/8	48	2 3/8	60	1	0.5
1 1/2	40	3 3/16	81	2 1/16	52	2 7/8	73	1.6	0.7
2	50	3 3/8	86	2 11/16	68	3 1/2	89	2.2	1



Typical Installations

Local codes shall govern installation requirements. To be installed in accordance with the manufacturer's instructions and the latest edition of the Uniform Plumbing Code. Not recommended for installation in sewage ejector piping or for reciprocating air compressor service.


Specifications

The In-Line Single Check Valve shall be rated for 400 WOG. The body shall be lead free brass, the seat gasket shall be NBR, and the spring shall be stainless steel (300 series). The In-Line Single Check Valve shall be a ZURN WILKINS Model 40XL2.


3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292


Rev. A Date: 8/13 Document No. BF-40XL2 Product No. Model 40XL2

MODEL 40 XL2 1/2" - 3/4"



MODEL 40XL2 1", 1 1/4 & 1 1/2"





www.zurn.com Page 2 of 2