

GP100 / GP250 USB

Electronic General Purpose Bench Scale



Replaces the traditional mechanical scales

- **Accuracy**– ± 3 displayed divisions
- **Power**– One 9V battery (included), AC adapter and USB cable (not included)
- **Portable**– Attached handle allows for easy transport
- **Internal Backlit Display**– Display is integrated into the scale base. 25 mm / 1" high backlit digits allow for easy visibility.
- **Communication**– USB virtual COM port (cable not included)
- **Weight Hold Key**– Locks the weight reading when a large package blocks the display
- **Discrete Switch Keyboard Technology**– Unique key button design to ensure reliability and longevity
- **Electro-Mechanical Design**– Ensures greater accuracy even at higher weight capacities

GP100 / GP250 USB Electronic General Purpose Bench Scale

Features

Construction: 22 gauge steel with ribbed base designed to protect against damage to the scale

Display: Four large 25 mm / 1" H digits, backlit LCD

Keyboard Functions:

Hold Freezes weight on the display only when a weight of 3 lbs or more is placed on the scale

TARE Removes weight of empty container or item placed on the scale to obtain a net weight

UNITS Scrolls between kilograms and pounds
Turns scale on or off and returns scale to zero weight

Indicator Displayed Messages:

L0 Battery is weak
After five minutes scale will turn off

Auto Zero Tracking:

Includes AZT (Auto Zero Tracking) at 0.5 or manual push button to reestablish zero reference when displayed weight is less than 2% of capacity

Overload Capacity: Capable of withstanding 200 kg or 400 lb of weight without damaging the scale

Auto Shutdown: To conserve battery life the display will shutdown after two minutes of non-use. Can be configured via the keypad for Off, two or four minutes.

Specifications

Capacity:

GP100 USB: 45 x 0.1 kg / 100 x 0.2 lb
GP250 USB: 110 x 0.2 kg / 250 x 0.5 lb

Accuracy: ± 3 displayed divisions

Power: Internal Battery: One 9 volt (included)
AC Adapter: 9 VDC @ 200 mA (not included)
USB cable (not included)

Operating Temperature: 5° C to 40° C / 42° F to 104° F

Product Dimension:

278 mm (L) x 318 mm (W) x 56 mm (H)
10.95" (L) x 12.50" (W) x 2.20" (H)

Product Weight: 3 kg / 6 lb

Packaging Dimension:

339 mm (L) x 318 mm (W) x 76 mm (H)
13.35" L x 13.5" W x 3" H

Shipping Weight: 4 kg / 8 lb

Agency Approvals: UL/CUL power adapter, FCC

Product Code:

GP100 USB: 816965006755
GP250 USB: 816965006731



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

