



**SAFETY DATA SHEET**

**SECTION I: PRODUCT & COMPANY IDENTIFICATION**

**PRODUCT NAME:** DRAIN PROTECTORS

(OIL797;OIL800;OIL801;OIL802;OIL803OIL810;OIL811;OIL812;OIL813;OIL815;  
OIL816; OIL818; OIL819)

**Distribution Location:**

Chemtex, Inc.

1 Front Street

Cumberland RI 02864

**Customer Service Telephone Number:** 1-401-305-3030

**Emergency phone number:** 1-877-431-0200

**Date Prepared:** 01/28/2015

**SECTION II: HAZARDOUS IDENTIFICATION**



Not considered a hazardous material at temperatures below melting point. Not considered a controlled substance or a carcinogen.

**SECTION III: COMPOSITION/INFORMATION ON INGREDIENTS**

<u>INGREDIENTS</u>	<u>PERCENT</u>	<u>CAS NUMER</u>	<u>OSHA PEL</u>	<u>ACGIH TLV</u>
Polyurethane Elastomer	100%	N/A	N/A	N/A

**SECTION IV: FIRST AID MEASURES**

**EYE CONTACT:** If irritation occurs flush the eye with plenty of water for at least 15 minutes. If irritation persists see a doctor.

**SKIN CONTACT:** Remove product from skin, wash with water as necessary

**INHALATION:** Remove to fresh air. If symptoms persist then contact physician

**INGESTION:** induce vomiting as directed by medical personnel

## SECTION V: FIRE FIGHTING MEASURES

<b>FLASH POINT:</b>	N/A
<b>AUTO IGNITION:</b>	N/A
<b>FLAMMABLE LIMITS:</b>	N/A
<b>FIRE EXTINGUISHING MEDIA:</b>	Water Spray, Foam, CO2, Dry Chemical
<b>SPECIAL FIRE FIGHTING PROCEDURES:</b>	Evacuate all non-emergency personnel to a safe location. Use self-contained breathing apparatus. Avoid breathing smoke, fumes or decomposition products. Use water spray to drench smoldering elastomer. Product may melt after ignition to form flammable liquids. Burning produces intense heat, dense smoke and toxic gases such as carbon monoxide, oxides of nitrogen and traces of hydrogen cyanide.

## SECTION VI: ACCIDENTAL RELEASE MEASURES

If material is released: pick up and handle as any other inert solid material  
Waste Disposal: Not considered a hazardous waste

## SECTION VII: HANDLING AND STORAGE

Always decontaminate after use. When not in use, store with plastic film applied for long life. Keep out of direct sunlight.  
Store in dry area. Do not store near open flame, high heat, strong oxidants, or halogenated hydrocarbons.  
Polyurethane, when heated, becomes very sticky and will burn. Use self-contained air masks to enter smoky area in the event of fire. Adequate ventilation is required to remove decomposition products when temperature exceeds melting point. Avoid contact with melted product.

## SECTION VIII: EXPOSURE CONTROLS/ PERSONAL PROTECTION

<b>RESPIRATORY PROTECTION:</b>	None Required
<b>VENTILATION:</b>	None Required
<b>PROTECTIVE GLOVES:</b>	None Required
<b>EYE PROTECTION:</b>	Safety glasses with side shields are recommended as a good practice for industrial safety.

## SECTION IX: PHYSICAL AND CHEMICAL PROPERTIES

<b>APPEARANCE AND ODOR:</b>	Solid with no odor
<b>SPECIFIC GRAVITY:</b>	1.05 – 1.26 (H <sub>2</sub> O = 1)
<b>BOILING POINT (C):</b>	N/A
<b>MELTING POINT (C):</b>	380° F - 450° F, will degrade above 300° F
<b>SOLUBILITY IN WATER:</b>	Insoluble
<b>EVAPORATION RATE:</b>	N/A
<b>VAPOR PRESSURE (mm Hg):</b>	N/A
<b>VAPOR DENSITY (Air = 1):</b>	N/A
<b>EXPLOSIVE PROPERTIES:</b>	N/A

## SECTION X: STABILITY AND REACTIVITY

<b>INCOMPATIBLE MATERIALS:</b>	Strong acids or bases
<b>CONDITION TO AVOID:</b>	None known
<b>HAZARDOUS DECOMPOSITION:</b>	Decomposition through burning produces fumes consisting of organic particulate, gaseous hydrocarbons, carbon dioxide, carbon monoxide and may contain traces of

toluene diisocyanate (TDI) or diphenylmethane diisocyanate (MDI), other isocyanates, curatives, hydrogen cyanide, acrolein and oxides of nitrogen.

**SECTION XI: TOXICOLOGICAL INFORMATION**

Under normal conditions not applicable.

**SECTION XII: ECOLOGICAL INFORMATION**

Under normal conditions not applicable.

**SECTION XIII: DISPOSAL CONSIDERATIONS**

Not considered a hazardous material. Dispose of material according to any local, state, and federal regulations.

**SECTION XIV: TRANSPORT INFORMATION**

Not regulated as a hazardous material.

**SECTION XV: REGULATORY INFORMATION**

CERCLA (Comprehensive Environmental Response Compensation and Liability Act):	Not reportable quantity
OSHA Hazard Communications Standard, 29 CFR 1910.1200:	No listed ingredient
SARA Title III (Superfund Amendments and Reauthorization Act):	No listed ingredient
TSCA (Toxic Substances Control Act):	All ingredients are listed

**SECTION XVI: OTHER INFORMATION**

NFPA Hazard Rating:	none – extreme	Health:	0	Reactivity:	0
	0 - 4	Fire:	1		

For more information:  
Phone (877) 431-0200 - Fax (401) 305-3030  
[www.chemtexinc.com](http://www.chemtexinc.com)