

Krynit Grip and Proof 600

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile GRIP&PROOF coating
- **Length (inches)** 9.05-11.02
- **Wrist** Knitted wrist
- **Colour/Color** Black
- **Interior finish** Seamless textile support from HDPE fibres
- **Exterior finish** Fully-coated
- **Size / EAN** 7 8 9 10
- **Packaging** 1 pair/bag - 12 pairs/bag - 48 pairs/carton
- **Complementary information** Guaranteed DMF free Guaranteed Silicone free on palm and fingers



PERFORMANCE RESULTS

Certification category 2



CUT



4343

ISO 13997 :
7 N (671 g)

ISO 13997 defines the weight on the blade required to cut in a single movement.


Data was obtained according to ISO 13997, from the average of several measurements. As Individual specimens will obviously have greater or lesser cut resistance than the average, so this result can provide only a general indication of the cut resistance of any protective material.

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



RADIOACTIVE CONTAMINATION EN 421




SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%




COLD HAZARDS EN 511

PERFORMANCE LEVELS



HEAT AND FIRE EN 407

PERFORMANCE LEVELS



For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONAL
www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Cut and oilproof. Fully dipped, repels oil penetration, reduce dermatitis while ensuring you cut protection
- Grip & Proof coating ensures an excellent grip in oily environments.
- Excellent abrasion resistance due to nitrile coating
- Unbeatable fingertip sensitivity.
- Long lasting and cost effective: washable until 5 cleaning cycles (see laundering and drying conditions)

MAIN FIELDS OF USE

Automotive/mechanical industry

- Pump manufacturing
- Machining parts using cutting oil
- Handling oily mechanical parts
- Handling and sorting small, sharp parts
- Bodywork assembly

Other industries

- Maintenance in wet environments
- Machine maintenance
- Glass working

Mechanical industry

- Maintenance in wet environments (water, oil, greases, hydrocarbons)
- Precision assembly
- Cutting and stamping metal

INSTRUCTIONS FOR USE

Instructions for use

It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.

- It is not recommended for persons sensitized to dithiocarbamates and to natural latex (wrist with elastic natural rubber).
- Put the gloves on dry, clean hands.
- Ensure the inside of the gloves is dry before putting them on again.
- Inspect the gloves for cracks or snags before reusing them.
- Do not use them next to moving machinery

Storage conditions

Store the glove in their original packaging protected from heat, light and humidity

Laundering conditions

Wipe gloves contaminated with oil or grease with a dry cloth before removing them. Performances of the gloves are not negatively affected by cleaning up to 5 cleaning cycles* under the conditions described above: Use of a household or industrial washing machine and a standard liquid detergent, synthetic program temperature 60 °C and spin drying at 400 rotations per minute. Improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

The customer or the launderer is sole responsible for the compliance with the washing conditions.

* Test performed: 5 successive washes on unworn gloves.

Drying conditions

Tumble drying at 60°C maximum. Ensure the inside of the gloves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/09/13/1082 ext 02/06/14

- Issued by the notified body nr

0075 - C.T.C - 4 rue Hermann Frenkel - 69367 LYON Cedex 07 France