

Krytech Wide Arm 539 W

DESCRIPTION AND GENERAL PROPERTIES

- **Length (inches)** 18
- **Thickness (inches)** ANSI Cut Level 2
- **Colour/Color** Grey
- **Interior finish** Seamless textile support from HDPE fibres
- **Packaging** 6 pairs/bag - 48 pairs/carton
- **Complementary information** One size only wide sleeve design / Tested according to the EN388 test methods



PERFORMANCE RESULTS

Certification category



CUT



334X
ISO 13997 :
7.6 N (731 g)


ISO 13997 defines the weight on the blade required to cut in a single movement.

Data was obtained according to ISO 13997, from the average of several measurements. As Individual specimens will obviously have greater or lesser cut resistance than the average, so this result can provide only a general indication of the cut resistance of any protective material.

Legends



MECHANICAL HAZARDS EN 388



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



RADIOACTIVE CONTAMINATION EN 421




SPECIFIC CHEMICAL PROTECTION EN 374


Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



COLD HAZARDS EN 511



HEAT AND FIRE EN 407



For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONNEL
www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Extra wide arm design and ultra thin thumb hole area provides better comfort while maintaining dexterity
- Velcro Adjustable strap for secure fit
- Performance of the sleeves are guaranteed up to 5 cleaning cycles

MAIN FIELDS OF USE

Automotive/mechanical industry

- Mechanical maintenance
- Assembly of thin metal sheets
- Automotive assembly
- Handling metal parts

Mechanical industry

INSTRUCTIONS FOR USE

Instructions for use

Not be used next to moving machinery.

The cuff must be worn associated with a glove with at minimum the same levels of protection.

Adjust the cuff on the arm with the Velcro® strap.

Caution: inappropriate sleeve usage or cleaning may alter performance level. For more information on sleeve usage or performances, contact your distributor or Mapa Professional Technical Customer Service (stc.mapaspontex@mapaspontex.fr)

Laundering conditions

Performances of the sleeves are guaranteed up to 5 cleaning cycles under the conditions described above: Use of a household or industrial washing machine and a standard liquid detergent, synthetic program temperature 60°C (140°F) and spin drying at 400 rotations per minute. It's advisable to attach the magic tape before to put the sleeve inside the washing machine. Improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

Drying conditions

Tumble drying at 60°C (140°F) maximum. Put the sleeves on dry and clean hands. Ensure the inside of the sleeves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).