



SAFETY DATA SHEET

SECTION I: PRODUCT & COMPANY IDENTIFICATION

PRODUCT NAME: Universal Needle-Punch Rug – (RNP/OILM6004/PBRNP)

Distribution Location:

Chemtex, Inc.

1 Front Street

Cumberland RI 02864

Customer Service Telephone Number: 1-401-305-3030

Emergency phone number: 1-877-431-0200

Date Prepared: 01/28/2015

SECTION II: HAZARDOUS IDENTIFICATION



GHS Classification: Not a dangerous substance according to GHS

POTENTIAL HEALTH EFFECTS:

Eye Contact: May cause irritation
Ingestion: No hazard in normal use of product
Inhalation: No hazard in normal use of product
Skin Contact: Not applicable
Chronic: Not applicable

SECTION III: COMPOSITION/INFORMATION ON INGREDIENTS

<u>INGREDIENTS</u>	<u>PERCENT</u>	<u>CAS NUMER</u>	<u>OSHA PEL</u>	<u>ACGIH TLV</u>
Polypropylene	>96%	9003-07-0	15mg/m ³	10 mg/m ³
Minor Additives*	<2%	Mixture	N/A	N/A
Surfactant	<1%	N/A	N/A	N/A
Pigment/Carbon Black	<1%	Mixture	N/A	N/A

* Proprietary Information/Trade Secret

SECTION IV: FIRST AID MEASURES

EYE CONTACT: No significant hazard identified. Particles or fibers may cause slight discomfort similar to a piece of dust in the eye. Use eyewash, consult physician if irritation persists.

SKIN CONTACT: No significant hazard identified. Particles or fibers may cause slight discomfort similar to sand on the skin. Wash area with water, consult physician if irritation persists.

INHALATION: No significant hazard identified

INGESTION: No significant hazard identified

SECTION V: FIRE FIGHTING MEASURES

FLASH POINT: >315° C (600° F)

AUTO IGNITION : >550° C (1022° F)

FIRE EXTINGUISHING MEDIA: Water, Foam, CO2, Dry Chemical

SPECIAL FIRE FIGHTING PROCEDURES: Standard procedure for Class A fires

UNUSUAL FIRE AND EXPLOSION HAZARDS: Overheated or molten material may burn slowly with dense smoke. Avoid inhalation of vapors. Sorbents will take on the characteristics/properties of whatever liquid is absorbed. Therefore, all measures must be taken as if you were handling the liquid itself. Sorbents do not make the liquid less hazardous. Always refer to the MSDS for the chemical absorbed before proceeding.

SECTION VI: ACCIDENTAL RELEASE MEASURES

Product is fabric made from polyolefin fibers and the roll may be very heavy. Use caution in the event of spill on uneven ground. Use suitable rated lifting equipment in the event a roll needs to be moved. Dispose of any damaged material in accordance with Local, State and Federal regulations.

SECTION VII: HANDLING AND STORAGE

Store in dry area. Do not store near open flame, high heat, strong oxidants, or halogenated hydrocarbons. Polypropylene, when heated, becomes very sticky and will burn. Use self-contained air masks to enter smoky area in the event of fire. Adequate ventilation is required to remove decomposition products when temperature exceeds melting point. Avoid contact with melted product.

Sorbents will take on the characteristics/properties of whatever liquid is absorbed. Therefore, all measures must be taken as if you were handling the liquid itself. Sorbents do not make the liquid less hazardous. Always refer to the MSDS for the chemical absorbed before proceeding

SECTION VIII: EXPOSURE CONTROLS/ PERSONAL PROTECTION

RESPIRATORS: None Required

PROTECTIVE GLOVES: None Required

EYE PROTECTION: Safety glasses with side shields are recommended as a good practice for industrial safety.

OTHER PROTECTIVE EQUIPMENT (SPECIFY): None Required

SECTION IX: PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE AND ODOR: Gray or black & virtually odor free

SPECIFIC GRAVITY (H²O=1): 0.905

BOILING POINT (C): N/A

MELTING POINT (C): 165° C (330° F)

SOLUBILITY IN WATER: Negligible, below 0.1%

EVAPORATION RATE: N/A

VAPOR PRESSURE (mm Hg): N/A

VAPOR DENSITY (Air = 1): N/A

EXPLOSIVE PROPERTIES: N/A

SECTION X: STABILITY AND REACTIVITY

GENERAL: This is a stable material
CONDITIONS OF REACTIVITY: N/A
INCOMPATIBLE MATERIALS: Strong oxidizing agents may degrade product over an extended period of time
CONDITION TO AVOID: N/A
HAZARDOUS DECOMPOSITION: When heated, it may emit toxic fumes
HAZARDOUS POLYMERIZATION: Will not occur

SECTION XI: TOXICOLOGICAL INFORMATION

LD50: N/A
LC50: N/A
CARCINOGENICITY: IARC: NO OSHA: NO
National Toxicology Program: NO
California Prop 65: No listed ingredient

SECTION XII: ECOLOGICAL INFORMATION

No data available

SECTION XIII: DISPOSAL CONSIDERATIONS

Disposal must be done in accordance with local, state and federal regulations based on chemicals adsorbed by products.

Sorbents will take on the characteristics/properties of whatever liquid is absorbed. Therefore, all measures must be taken as if you were handling the liquid itself. Sorbents do not make the liquid less hazardous. Always refer to the MSDS for the chemical absorbed before proceeding.

SECTION XIV: TRANSPORT INFORMATION

DOT (Department of Transportation):

Proper shipping Name: Not regulated
Hazard Class: None
Identification Number: Not applicable

SECTION XV: REGULATORY INFORMATION

CERCLA (Comprehensive Environmental Response Compensation and Liability Act): Not reportable quantity
OSHA Hazard Communications Standard, 29 CFR 1910.1200: No listed ingredient
SARA Title III (Superfund Amendments and Reauthorization Act): No listed ingredient
TSCA (Toxic Substances Control Act): All ingredients are listed

SECTION XVI: OTHER INFORMATION

NFPA Hazard Rating: none – extreme Health: 0 Reactivity: 0
0 - 4 Fire: 1

For more information: Phone (877) 431-0200 - Fax (401) 305-3030 www.chemtexinc.com