

Solo Green 977

DESCRIPTION AND GENERAL PROPERTIES

- Material Nitrile
- Length (inches) 9.5
- Thickness (inches) .004 (4 mil)
- Wrist Rolled cuff
- Colour/Color Green
- Interior finish Chlorinated
- Exterior finish Smooth with pebbled fingertips
- Size / EAN 6 7 8 9 10
- Packaging 100 gloves/box - 1000 gloves/carton



PERFORMANCE RESULTS

Certification category 3

CE 0334




Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



RADIOACTIVE CONTAMINATION EN 421




SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%




COLD HAZARDS EN 511

PERFORMANCE LEVELS



HEAT AND FIRE EN 407

PERFORMANCE LEVELS



For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONAL
www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Suitable for a wide range of chemical (see the chemical resistance chart)
- Good compromise between thickness, suppleness and resistance
- Chlorinated for a better doning
- Pebbled on fingertips for a good grip

MAIN FIELDS OF USE

Cosmetics and Pharmaceutical industry

- Handling in laboratories

Chemical industry

- Sampling chemicals

Laboratory

- Pharmaceutical preparation

INSTRUCTIONS FOR USE

Instructions for use

It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.

- It is not recommended for persons sensitized to dithiocarbamates .
- Put the gloves on dry, clean hands.

Storage conditions

Store the gloves in their original packaging protected from direct sunlight, far from heat sources.

Laundering conditions

These gloves are designed for single use only.

Food contact US

FDA 21CFR 177.2600

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/09/15/0984

- Issued by the notified body nr

0075-CTC- 4 rue Hermann Frenkel - 69367 Lyon Cedex 07 - France

- Quality assurance certificat

0334 - Asqual 14 rue des Reculettes -75013 Paris - France