

Stansolv AK-22 381

DESCRIPTION AND GENERAL PROPERTIES

- Material Nitrile
- Length (inches) 14
- Thickness (inches) 0.033 (Med. Wt.)
- Wrist Scalloped cuff
- Colour/Color Green
- Interior finish Textile support Mapa Technology
- Exterior finish Embossed texture
- Size / EAN 7 8 9 10 11
- Packaging 12 pairs/bag - 72 pairs/carton
- Complementary information Guaranteed without silicone



PERFORMANCE RESULTS

Certification category 3

CE 0334



X1XXXX



AJKL




3121

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%




RADIOACTIVE CONTAMINATION EN 421




COLD HAZARDS EN 511

PERFORMANCE LEVELS



HEAT AND FIRE EN 407

PERFORMANCE LEVELS



For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONAL
www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Extremely supple, due to the unique Mapa multi-layer process
- Embossed texture for better grip of wet objects
- Added comfort and thermal insulation, due to the cotton-knit lining

MAIN FIELDS OF USE

Automotive/mechanical industry

- Surface treatment
- Part degreasing
- Automotive assembly

Other industries

- Machine maintenance
- Laboratory tests

Chemical industry

- Handling drums of chemical products
- Chemical product blending
- Manipulating valves

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at the workplace may differ from the «CE»-type tests.
- It is not recommended for persons sensitized to dithiocarbamates and thiazoles to use these gloves.
- Put the gloves on dry, clean hands.
- Do not use the gloves in contact with a chemical for a duration in excess of the measured breakthrough time. Refer to the website www.mapa-pro.com or contact the Technical Customer Service - MAPA PROFESSIONNEL (stc.mapaspontex@mapaspontex.fr) in order to know this breakthrough time. Use 2 pairs alternatively when in long duration contact with a solvent.
- Turn the cuff end down in order to prevent a hazardous chemical from dripping onto the arm.
- Inspect the gloves for cracks or snags before reusing them.

Storage conditions

Store the gloves in their packaging protected from light and humidity.

Laundering conditions

Before taking off the gloves, clean them as appropriate :

- in use with paints, pigments and inks: wipe with a clean cloth dampened with a suitable solvent, and rub over with a dry cloth
- in use with a solvent (diluent, etc...): rub over with a dry cloth
- in use with acids or alkalis: thoroughly rinse the gloves under running water, and rub over with a dry cloth.

Caution : improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

Drying conditions

Ensure the inside of the gloves is dry before putting them on again.

Food contact US

FDA 21CFR 177.2600

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate
0075/014/162/09/11/0492 ext 01/09/11
- Issued by the notified body nr
0075

C.T.C. – 4 rue Hermann Frenkel - F- 69367 LYON Cedex 07

- Quality assurance certificat
0334 Asqual 14 rue des Reculettes -F-75013 PARIS