

# Belt Grinder



**Model G-75**  
6,600 fpm

## BELT GRINDER

With 6,600 fpm grinding speed and a 4 HP motor, our belt grinder is designed for maximum metalworking efficiency. The head pivots up and down for easy work height adjustments to adapt to the job at hand. A hinged top cover opens for access to grind large pieces of metal.

## SPECIFICATIONS

### G-75

Number	961001
Belt size	3" x 79"
Horsepower	4
Electrics	220V/440V*, 3 phase
Contact wheel size	3" x 8"
Belt speed	6,600 fpm
Grinding plane (full)	3" x 21"
Weight	250 lbs

*\*440V model requires step-down transformer for operation (part number: 300674)*



MODEL G-75

### FEATURES

- ✓ Pivots up and down on the base for easy ergonomic work height adjustments.
- ✓ Advanced belt tracking with vented front wheel fixed in place for rigidity when grinding on the wheel radius.
- ✓ Hinged top cover opens for access to grind large pieces using the entire length of the belt.
- ✓ Adjustable parts rest and backing plate with Plexiglass shield to keep the part being ground steady and in place

### MODEL OPTIONS

- ✓ Belt- 40 grit sold per belt
- ✓ Belt- 60 grit sold per belt

### STANDARD EQUIPMENT

- ✓ Base
- ✓ Hinged Cover
- ✓ Grinding Belt
- ✓ Plexiglas Guarding
- ✓ 60 Grit Belt