

Specifications:

- **Motor:**
1/16 HP Universal
- **Speed:** 17,000 RPM
(2,000 to 17,000
with 2-248 rheostat
0 – 17,000 with
1-310 table top
speed control.)
- **Chuck:** 5/32" capacity
geared chuck
- **Dimensions:**
Chuck to table 4" maximum
Table Feed 1-5/8"
Table Diameter 3-1/2"
Drills to center of 6" Circle
Height 17" maximum
- **Weight:** Net 9 lbs.
Ship Weight 14 lbs.
- **Power Source:**
115V AC/DC

Optional Accessories:

- 2-248 Foot control
rheostat
- 1-310 table-top speed
control

Series 16 Sensitive Drill Unit Model 8576-210

Quality is our Legacy

DUMORE CORPORATION

Compact and light weight, this bench type sensitive drill press is a rigid, stationary unit designed to consistently drill exceptionally precise small holes. Large, adjustment wheels provide for easy finger tip control. Hand fed table moves work to drill while Hole Depth Adjustment Collar maintains selected depth repeatedly. Three inch throat and swing away table add to its versatility. There are also optional accessories available to control the drill's speed.



DUMORE CORPORATION

1030 Veterans Street
Mauston, WI 53948

Phone: 888-467-8288

Fax: 800-338-6673

E-mail:

sales@dumorecorp.com

 **DUMORE CORPORATION**
Quality is our legacy