

Temp-Ice 700

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile GRIP&PROOF coating
- **Length (inches)** 9.50
- **Thickness (inches)** Hvy. Wt.
- **Wrist** Knitted wrist
- **Colour/Color** Black / Blue
- **Interior finish** Knitted thermal protection
- **Exterior finish** Non-slip grip
- **Size / EAN** 7 8 9 10
- **Packaging** 1 pair/bag - 12 pairs/bag - 72 pairs/carton



PERFORMANCE RESULTS

Certification category 2



CUT



02X



3222X
ISO 13997 :
N (690 g)

ISO 13997 defines the weight on the blade required to cut in a single movement.

Data was obtained according to ISO 13997, from the average of several measurements. As individual specimens will obviously have greater or lesser cut resistance than the average, so this result can provide only a general indication of the cut resistance of any protective material.

Legends


EN 388

MECHANICAL HAZARDS



PERFORMANCE LEVELS


0-4 0-5 0-4 0-4 A-F (P)



THERMAL RISKS
heat and fire

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4



CHEMICAL RISKS

EN ISO 374-1

Type A



U V W X Y Z

- A Methanol
- B Acetone
- C Acetonitrile
- D Dichloromethane
- E Carbon Disulfide
- F Toluene
- G Diethylamine
- H Tetrahydrofurane
- I Ethyl acetate

EN ISO 374-1

Type B



X Y Z

- J n-Heptane
- K Sodium hydroxide 40%
- L Sulphuric acid 96%
- M Nitric acid 65%
- N Acetic acid 99%
- O Ammonia 25%
- P Hydrogen peroxide 30%
- S Hydrofluoric acid 40%
- T Formaldehyde 37%

EN ISO 374-1

Type C



MICRO-ORGANISMS

EN ISO 374-5



Protection against bacteria, fungi

EN ISO 374-5



Protection against bacteria, fungi, virus

VIRUS


EN 511



COLD HAZARDS

PERFORMANCE LEVELS

0-4 0-4 0 or 1



EN 421



RADIOACTIVE CONTAMINATION



CUT

CUT RESISTANCE

- | | | |
|-------------|-------------|-------------|
| A1 ≥ 200 G | A4 ≥ 1500 G | A7 ≥ 4000 G |
| A2 ≥ 500 G | A5 ≥ 2200 G | A8 ≥ 5000 G |
| A3 ≥ 1000 G | A6 ≥ 3000 G | A9 ≥ 6000 G |

For more details: www.mapa-pro.com



DESCRIPTION AND GENERAL PROPERTIES

- Coating 5 times as durable than standard gloves on the market
- Excellent grip when handling wet parts
- Stay dry when working in wet conditions
- Washable until 5 cleaning cycles (see laundering and drying conditions)
- Suitable for frozen, dry and some fatty foods use according to the French law of November 9th, 1994 and to the European Directive CEE 1935/2004

MAIN FIELDS OF USE

Transport, logistics

- Order preparation

Other industries

- Maintenance in wet or cold environments
- Construction materials handling

Local Authorities (Waste Collection and Processing)

- Waste collection

Local Authorities (Catering Services)

Local Authorities (Parks and Public Spaces)

- Public park maintenance

Local Authorities (Roads and Highways)

- Maintaining the roads

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.
- It is not recommended for persons sensitised to natural rubber latex or dithiocarbamates to use these gloves.
- Put the gloves on dry, clean hands.
- Ensure the inside of the gloves is dry before putting them on again.
- The gloves may lose their insulating property in the wet state.

Storage conditions

Store the glove in their original packaging protected from heat, light and humidity.

Laundering conditions

Wipe gloves contaminated with oil or grease with a dry cloth before removing them. Performances of the gloves are not negatively affected by cleaning up to 5 cleaning cycles* under the conditions described above: Use of a household or industrial washing machine and a standard liquid detergent, synthetic program temperature 60 ° C and spin drying at 400 rotations per minute. Improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

The customer or the launderer is sole responsible for the compliance with the washing conditions.

* Test performed: 5 successive washes on unworn gloves.

Drying conditions

Trumble drying at 60°C maximum Put the gloves on dry, clean hands. Ensure the inside of the gloves is dry before putting them on again.

Food contact US

FDA 21CFR 177.2600

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/04/14/0344

- Issued by the notified body nr

0075

CTC - 4 rue Hermann FENKEL - F 69367 LYON CEDEX 07