

# Trilites Bagged 994

## DESCRIPTION AND GENERAL PROPERTIES

- **Material** Natural latex, neoprene and nitrile
- **Length (inches)** 10
- **Thickness (inches)** 0.006 (6 mil)
- **Wrist** Rolled cuff
- **Colour/Color** Purple
- **Interior finish** Chlorinated
- **Exterior finish** Pebbled
- **Size / EAN** 6 S 7 M 8 L 9 XL
- **Packaging** 100 gloves/bag - 1000 gloves/carton
- **Complementary information** Guaranteed without silicone



## PERFORMANCE RESULTS

Certification category 3

CE 0334



### Legends



**MECHANICAL  
HAZARDS  
EN 388**

PERFORMANCE LEVELS

0-4 0-5 0-4 0-4  
 — Puncture resistance  
 — Tear resistance  
 — Blade cut resistance  
 — Abrasion resistance



**LOW CHEMICAL  
PROTECTION  
EN 374**



**MICRO-ORGANISMS  
EN 374**



**RADIOACTIVE  
CONTAMINATION  
EN 421**



**HEAT  
AND FIRE  
EN 407**

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4  
 — Resistance to large quantities of molten metal  
 — Resistance to small drops of molten metal  
 — Radiant heat resistant  
 — Convective heat resistance  
 — Contact heat resistance  
 — Burning behaviour



**SPECIFIC CHEMICAL  
PROTECTION  
EN 374**

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



**COLD HAZARDS  
EN 511**

PERFORMANCE LEVELS

0-4 0-4 0 or 1  
 — Water permeability  
 — Contact cold resistance  
 — Convective cold resistance

For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

**MAPA**  
PROFESSIONAL  
[www.mapa-pro.com](http://www.mapa-pro.com)

## DESCRIPTION AND GENERAL PROPERTIES

- Unique triple polymer blend for enhanced comfort and resistance.
- Protection against chemical splashes.
- Optimal thickness delivering maximum tactility with superior durability.
- User traceability on inner boxes and cartons.

## MAIN FIELDS OF USE

### Laboratory

- Manufacturing of medicines
- Pharmaceutical preparation
- Research, analysis, handling of precision parts
- Research, analysis, manipulation of precision parts, optical processes

## INSTRUCTIONS FOR USE

### Instructions for use

- These gloves are designed for single use only.
- It is not recommended for persons sensitised to natural latex, dithiocarbamates and thiazoles to use these gloves.
- Put the gloves on dry, clean hands.

### Storage conditions

Store the gloves in their packaging in cool dry place

### Food contact US

FDA 21CFR 177.2600

## LEGISLATION

This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council.

This product does not contain any substances of very high concern according to the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0072/014/162/07/04/0128

- Issued by the notified body nr

I.F.T.H \_ Av Guy de Collongue\_69134 ECULLY CEDEX

- Quality assurance certificat

0334 Asqual 14 rue des Reculettes -F-75013 PARIS