

DUMORE CORPORATION

High quality, long lasting tools, since 1913.

Series 6-511 (High Speed) Flex Shaft Grinder Model 8565-210

This flex shaft grinder has a versatile combination of high speed and high horsepower that provides:

- The speed required for light work such as contouring and polishing jobs.
- The torque needed for heavier grinding and filing.
- The speed and torque required for heavy duty metal removal with carbide burrs.

Specifications:

- ◆ **Motor:** ¼ HP Universal
- ◆ **Speed:** 26,000 RPM (No Load)
- ◆ **Chuck:** 1/8" and 1/4" Collets
- ◆ **Power Source:** 115V AC/DC
- ◆ 2-206 Handpiece
- ◆ 6-214 Flex-Shaft

Optional Accessories:

- ◆ 2-248 Rheostat foot control (Part No. 852-0034)
- ◆ 1-310 Table-Top speed Control (Part No. 852-0033)



DUMORE CORPORATION

1030 Veterans Street
Mauston, WI 53948

Phone: 888-467-8288

Fax: 800-338-6673

E-mail: sales@dumorecorp.com

