





MASTER MAC-30BCT 30" High Velocity Floor Fan—8500 CFM, 1/3 HP, 120 Volt



- **DURABLE**—great for garages, barns, or workshops, or outside events
- **POWERFUL**—steel construction
- **INDUSTRY-LEADING**—high airflow for up to 8500 CFM
- Machined industrial motor, OSHA-compliant safety grille, swivel cart, and more
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than MASTER's industry-leading 30" High Velocity Floor Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting steel construction. Plus, the convenient swivel cart gives you maximum versatility. Whether you're in the barn, relaxing at home, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. MASTER – built for power.



Features and Benefits

- Great for garages, barns, or workshops, or outside events
- Powerful steel construction
- High airflow for up to 8500 CFM
- 1/3 HP enclosed motor
- Versatile swivel cart
- Rock-solid, OSHA-compliant safety grille
- 3 variable speed settings
- Large wheels for easy portability
- 1-year limited warranty

Key Specs

Model Number	MAC-30BCT
Brand	MASTER
Warranty	1-year limited warranty
Net Weight (lb.)	31
Air Flow (CFM)	6000 / 7000 / 8500
Motor Size (HP)	1/3

Variable Speed	Yes
Volts	120
Amps	2.2
Dimensions (L x W x H) (in.)	37 x 10 x 37