



Honeywell Miller Titan[™] II Harnesses & Lanyards Enhanced Adjustability for Improved Comfort

Honeywell Miller Titan™ II Harnesses & Lanyards

Enhanced Adjustability for Improved Comfort

Features & Benefits

- Easier vertical adjustability that stays in place, slip resistant back D-ring pad and forward positioned side D-rings, keeping your tool bags in the right place
- More comfort and better fit with lighter, strategically-placed padding that provides optimal airflow
- Increased worksite safety with Hi-Viz color webbing and ANSI Z359.11 compliance
- Quick availability with in-stock items

The new economical Miller Titan™ II line of harnesses offers enhanced adjustability, improved comfort and increased worksite safety. This next generation of Titan harnesses from Honeywell Industrial Safety is an affordable fall protection solution for the general construction, manufacturing and oil & gas (refinery) markets.

- Expanded Product Line
- New ANSI Z359.11 Compliant
- Maximum capacity 400-lbs. (181.4 kg)





Titan™ II Contractor

Construction-Style Harness

Designed for more comfort and better fit with lighter, strategically-placed padding that provides optimal airflow while working at heights.





Integrated Back/Shoulder Pad Offers optimal airflow allowing for increased comfort while carrying a full load of tools







Double Slot Side D-Rings Forward position allows for tools to be placed conveniently at your side











TITAN™ II NON-STRETCH	TITAN™ II NON-STRETCH	TITAN™II NON-STRETCH	TITAN™ II NON-STRETCH	TITAN™ II NON-STRETCH	TITAN™ II CONTRACTOR
T2000/UAK	T4000/UAK	T4007/UAK	T4500/UAK	T4507/UAK	T4577/UAK
T2007/UAK	T4000FD/UAK	T4007FD/UAK	T4500FD/UAK	T4507FD/UAK	
Shown above					


Shown above T2000/UAK

TITAN™II T-FLEX	TITAN™ II T-FLEX	TITAN™ II T-FLEX	TITAN™II T-FLEX
TF4000/UAK	TF4007/UAK	TF4500/UAK	TF4507/UAK
TF4000FD/UAK	TF4007FD/UAK	TF4500FD/UAK	Shown above
Shown above	Shown above	Shown above	T4507/UAK
Shown above	Shown above	Shown above	11001701

TITAN [™] II NON-STRETCH HARNESS	TITAN™ II T-FLEX HARNESS								
SKU	SKU	Back D-Ring	Front D-Ring	Side D-Rings	Chest Strap Buckles	Shoulder Strap Buckles	Leg Strap Buckles	Shoulder/Waist Padding	Removable Tool Belt
T2000/UAK	N/A	Yes	No	No	Mating	N/A	Mating	No	No
T2007/UAK	N/A	Yes	No	Yes	Mating	N/A	Mating	No	No
T4000/UAK	TF4000/UAK	Yes	No	No	Mating	Friction	Mating	No	No
T4000FD/UAK	TF4000FD/UAK	Yes	Yes	No	Mating	Friction	Mating	No	No
T4007/UAK	TF4007/UAK	Yes	No	Yes	Mating	Friction	Mating	No	No
T4007FD/UAK	TF4007FD/UAK	Yes	Yes	Yes	Mating	Friction	Mating	No	No
T4500/UAK	TF4500/UAK	Yes	No	No	Mating	Friction	Tongue	No	No
T4500FD/UAK	TF4500FD/UAK	Yes	Yes	No	Mating	Friction	Tongue	No	No
T4507/UAK	TF4507/UAK	Yes	No	Yes	Mating	Friction	Tongue	No	No
T4507FD/UAK	N/A	Yes	Yes	Yes	Mating	Friction	Tongue	No	No
TITAN" II CONTRAC	TOR HARNESS	<u>'</u>							
T4577/UAK	N/A	Yes	No	Yes	Mating	Friction	Tongue	Yes	Yes

The new Miller Titan™ II line of lanyards is economical and features Hi-Viz color for increased worksite safety and quick availability with in-stock items. All connectors are rated at 3,600-lb. gate-strength.





*Available in lengths from 4-ft. (1.2 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.



TITAN™ II STRETCH TUBULAR BUILT-IN SHOCK-ABSORBING LANYARDS							
T5122SS-Z7/6FTAF	Two	Locking snap hook	Large locking rebar hooks	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)			
T5111SS-Z7/6FTAF	One	Locking snap hook	Locking snap hook	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)			
T5121SS-Z7/6FTAF	Two	Locking snap hook	Locking snap hooks	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)			
T5112SS-Z7/6FTAF	One	Locking snap hook	Large locking rebar hook	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)			

*Available in lengths from 4-ft. (1.2 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.



TITAN™ II PACK-TYPE SHOCK-ABSORBING LANYARDS						
T6122-Z7/6FTAF	Two	Locking snap hook	Large locking rebar hooks	6-ft. (1.8 m)		
T6111-Z7/6FTAF	One	Locking snap hook	Locking snap hook	6-ft. (1.8 m)		
T6121-Z7/6FTAF	Two	Locking snap hook	Locking snap hooks	6-ft. (1.8 m)		
T6112-Z7/6FTAF	One	Locking snap hook	Large locking rebar hook	6-ft. (1.8 m)		

*Available in lengths from 3-ft. (0.91 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.



TITAN™ II STRETCH PACK-TYPE SHOCK ABSORBING LANYARDS						
T6122SS-Z7/6FTAF	Two	Locking snap hook	Large locking rebar hooks	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)		
T6111SS-Z7/6FTAF	One	Locking snap hook	Locking snap hook	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)		
T6121SS-Z7/6FTAF	Two	Locking snap hook	Locking snap hooks	Contracts 6-ft. (1.8 m) to 4-ft. (1.2 m)		
T6112SS-Z7/6FTAF	One	Locking snap hook	Large locking rebar hook	Contracts 6-ft. (1.8 m) to 4-ft.(1.2 m)		

*Available in lengths from 3-ft. (0.91 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.



TITAN [™] II POSITIONING LANYARDS						
T9111W-Z7/6FTAF	One	Locking snap hook	Locking snap hook	6-ft. (1.8 m)		
T9112W-Z7/6FTAF	One	Locking snap hook	Large locking rebar hook	6-ft.(1.8 m)		

*Available in lengths from 2-ft. (.6 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.



TITAN™ II TIE-BACK LANYARDS with Pack-Type Shock Absorber					
T6121TB-Z7/6FTAF	Two	Locking snap hook	Auto-lock carabiners; Forged sliding D-rings	6-ft. (1.8 m)	
T6111TB-Z7/6FTAF	One	Locking snap hook	Auto-lock carabiners; Forged sliding D-rings	6-ft. (1.8 m)	

*Available in lengths from 3-ft. (0.91 m) to 10-ft. (3 m). Locking Snap Hook – 3/4-in. (19 mm) gate opening. Large locking rebar hook – 2-1/2-in. (64 mm) gate opening.

 $All\ connectors\ include\ 3,600-lb.\ gate-strength.\ All\ Miller\ brand\ fall\ protection\ products\ meet\ applicable\ OSHA,\ ANSI\ and\ CSA\ requirements$ $For CSAZ259\ models, when\ ordering\ add\ a\ "C"\ at\ the\ end\ of\ the\ model\ number, ie.:\ T5122-Z7/6FTAFC, with\ the\ exception\ of\ T9111W-Z7/6FTAF,\ T9112W-Z7/6FTAF in\ the\ end\ of\ end\ of\ the\ end\ of\ the\ end\ of\ the\ end\ of\ end\ of\ end$ which the SKU does not change to meet CSA.

Limitless Possibilities. Ask the Expert. www.millerfallprotection.com

Technical Service: 800.873.5242

Honeywell Industrial Safety

900 Douglas Pike Smithfield, RI 02917

CANADA Tel: 800.430.5490

Tel: 888.212.7233 Fax: 800.322.1330 Fax: 888.667.8477 ▲ WARNING! This equipment should only be used after reading and understanding the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.

LMBT L 3/16 © 2016 Honeywell International Inc.



