

7000/9000 Series Combo Stacked Cartridge/Filters



The 7140 combines the 7100 organic vapor cartridge, the 7920 piggyback adapter and the 7940 P100 particulate filter disk.

The 7640 combines the 7600 multi-gas/vapor Smart® cartridge, the 7920 piggyback adapter and the 7940 P100 particulate filter disk.

Cost Savings

7140 and 7640 come pre-assembled but, unlike competitive models, they can be easily disassembled. This feature enables the user to replace either the filter or the cartridge or both as they become used up which helps to save money and reduces waste. With other brands, users are forced to discard the entire unit.

Convenience

Pre-assembled units save time and reduce the chance of error in selecting or assembling cartridge/filter combinations. Simply remove from the bag and attach to the respirator.

Applications

The Moldex 7140 and 7640 combo stacked cartridge/filters are useful in a variety of applications including petrochemical, construction, transportation, and chemical manufacturing.



COMBO STACKED CARTRIDGE/FILTERS

- For use with Moldex 7000 half mask respirator and Moldex 9000 full face respirator.
- All product and packaging material is 100% PVC-Free, for a greener alternative.

Packaging

Part #	Description	Quantity	Case
7140	Organic Vapor Cartridge/P100	1 pair per Bag	30 pairs
7640	Multi-Gas/Vapor Smart® Cartridge/P100	1 pair per Bag	30 pairs



7140



7640



IMPORTANT NOTICE TO USERS

You are responsible to understand and follow all warnings, restrictions and other information contained in the instruction manual before you enter a contaminated work area. Failure to do so may result in sickness or death.

APPLICATIONS

USE AGAINST

1. Contaminants specified on NIOSH approval label, matrix, cartridges or filters and in accordance with all limitations and applicable safety and health regulations, including OSHA.
2. Contaminants with good warning properties, i.e., smell, taste or irritation.

DO NOT USE AGAINST

1. Concentrations of contaminants which are unknown, or are immediately dangerous to life or health.
2. Concentrations of contaminants which exceed the maximum use concentration or 10x times the OSHA Permissible Exposure Limit, (PEL), when qualitatively fit tested, or 50x times the PEL only for the 9000 Full Face when quantitatively fit tested, or according to applicable government regulations.
3. Gases or vapors with poor warning properties or those which generate high heats of reaction, or paint sprays containing isocyanates.
4. Sandblasting.
5. Oil-based mists with N filters.

RESTRICTIONS

1. This respirator does not supply oxygen and must not be used in atmospheres containing less than 19.5% oxygen.
2. Do not remain in contaminated area if any physical distress occurs, for example breathing difficulty, dizziness or nausea.
3. Leave contaminated area and replace respirator and/or cartridge or filter if it is damaged, distorted, a proper fit cannot be obtained, you taste, smell or become irritated by contaminants, or breathing becomes difficult.
4. Do not alter, modify, or abuse this respirator.
5. Store respirator in sealed bag in a clean, dry, non-contaminated area.
6. Dispose of facepiece, and/or cartridges and disks/filters according to your employer's policy and applicable regulations.
7. N, R or P filters are required for particulates.
8. Where oil mists are present, either alone or in combination with solid particulates, do not use the R or P filters for longer than one eight-hour work shift. Dispose no later than eight hours after first use. Do not exceed 10x or 50x PEL (see Do Not Use Against, item 2) and 200 mg loading per respirator. It is the user's responsibility to know the PEL and concentration of the contaminant, the maximum work rate of the employee, and any other work site-specific information to calculate the loading of the filter. Where oil mists are present do not use N filters.
9. Dispose of all cartridges and N filters no later than thirty days after a) first use, and/or b) removing from sealed bag.
10. Use cartridges, filters, and facepieces before the "use by" expiration date printed on box or bag.

WARNINGS TO USER

1. Follow all instructions and warnings on the use of this respirator and wear during all times of exposure. Failure to do so will reduce respirator effectiveness, wearer protection, and may result in sickness or death.
2. For proper use, ask your supervisor or call +1 (800) 421-0668 or +1 (310) 837-6500, ext. 512/550.
3. The user must first be trained by the employer in proper respirator use, in accordance with applicable safety and health standards, for the contaminant and exposure level in the assigned work area. A written Respiratory Training Program must be in place and followed by each user before first use. It must meet all requirements of all applicable standards, including OSHA 29 CFR 1910.134, and in Canada CSA Z 94.4, e.g. training, fit testing, medical evaluation, and applicable OSHA substance specific standards.
4. The vapors, gases, dusts, mists, fumes, and other contaminants which can be dangerous to your health include those which you cannot see, taste, or smell.
5. Check with your supervisor for the appropriate cartridges and/or filters for the contaminants in your work area.
6. A qualitative or quantitative fit test must be performed before a respirator is assigned. Refer to current OSHA 29 CFR 1910.134 (f).

TECHNICAL SERVICE LINE

Moldex maintains a toll-free Technical Service Line to answer questions about the use of Moldex respirators, contaminants and regulations. If you have any questions call +1 (800) 421-0668 or +1 (310) 837-6500, ext. 512/550.

LIMITED WARRANTY – IMPORTANT NOTICE TO PURCHASER

This limited warranty is made in lieu of the warranties of merchantability, fitness for particular purposes and all other warranties, express or implied. There are no other warranties which extend beyond the description on the face hereof. The physical standards and specifications of Moldex will be met by products sold. Exclusive Remedies: damages for the breach of this limited warranty are limited to the replacement of such quantity of Moldex products proved to be defectively manufactured. Except as provided above, Moldex shall not be liable or responsible for any loss, damage, or liability, direct, indirect, incidental, special, or consequential, arising out of sale, use, or misuse, or the inability to use products by the user.

DISTRIBUTED BY:

MOLDEX-METRIC, INC.

10111 W. Jefferson Blvd., Culver City, CA 90232
Tel: +1 (800) 421-0668 or +1 (310) 837-6500
Fax: +1 (310) 837-9563
Email: sales@moldex.com www.moldex.com

CANADIAN CUSTOMER SERVICE

Tel: +1 (800) 421-0668, Ext. 517
Fax: +1 (310) 837-9563

Moldex, Ideas that wear well, the PVC-Free logo and Smart are registered trademarks. U.S. Patents Pending.

7140-807 REV B 08/11



MOLDEX
Ideas that wear well.