

Butoflex 650

| Chemical Product | CAS # | BTT (minutes) | Permeation level | Standard | Degradatio level | Rating |
|--|------------|---------------|------------------|---------------|------------------|--------|
| 2-Propanol (Isopropanol) 99% | 67-63-0 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acetic acid 10% | 64-19-7 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acetic acid 50% | 64-19-7 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acetic acid 99% | 64-19-7 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acetone 99% | 67-64-1 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acetonitrile 99% | 75-05-8 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Acrylic acid 95% | 79-10-7 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Acrylic acid 99% | 79-10-7 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Ammonia 99% | 7664-41-7 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Carbon disulfide 99% | 75-15-0 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Chlorine 100% | 7782-50-5 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Dichloromethane (Methylene Chloride) 99% | 75-09-2 | 12 | 1 | EN 374-3:2003 | 2 | = |
| Diethylamine 98% | 109-89-7 | 11 | 1 | EN 374-3:2003 | 2 | = |
| Dimethylformamide 99% | 68-12-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Ethanol 95% | 64-17-5 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Ethyl acetate 99% | 141-78-6 | 240 | 4 | EN 374-3:2003 | 4 | ++ |
| Ethyl methacrylate 99% | 97-63-2 | 81 | 3 | ASTM F739 | NT | NA |
| Formic Acid 100% | 64-18-6 | NT | NT | | 4 | NA |
| Formic Acid 96% | 64-18-6 | NT | NT | | 4 | NA |
| Hydrochloric acid 10% | 7647-01-0 | NT | NT | | 4 | NA |
| Hydrochloric acid 35% | 7647-01-0 | NT | NT | | 4 | NA |
| Hydrochloric acid 37% | 7647-01-0 | NT | NT | | 4 | NA |
| Hydrofluoric Acid 10% | 7664-39-3 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Hydrofluoric Acid 49% | 7664-39-3 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Hydrogen bromide 100% | 10035-10-6 | NT | NT | | 4 | NA |
| Hydrogen bromide 47% | 10035-10-6 | NT | NT | | 4 | NA |

*not normalized result

Overall Chemical Protection Rating

Protection rating is determined by taking into account the effects of both permeation and degradation in an attempt to provide users with an overall protection guideline when using our glove products against specific chemicals.

- Used for **high chemical exposure** or chemical immersion, limited to BTT based on a working day.
- Used for **repeated chemical contact**, limited to total chemical exposure i.e. : accumulative BTT based on a working day.
- **Splash protection only**, on chemical exposure the gloves should be discarded and new gloves worn as soon as possible.
- **Not recommended**, these gloves are deemed unsuitable for work with this chemical.

 NT : Not tested

 NA : Not applicable because not fully tested (only degradation OR permeation results)

The chemical test data and overall chemical protection rating should not be used as the absolute basis for glove selection. Actual in-use conditions may vary glove performance from the controlled conditions of laboratory tests. Factors other than chemical contact time, such as concentration and temperature, glove thickness and glove reuse, may also affect performance. Other glove requirements, such as length, dexterity, cut, abrasion, puncture and snag resistance, or glove grip also need to be considered in making your final selection.

Butoflex 650

| Chemical Product | CAS # | BTT (minutes) | Permeation level | Standard | Degradatio level | Rating |
|--------------------------------------|------------|---------------|------------------|---------------|------------------|--------|
| Hydrogen chloride 99% | 7647-01-0 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Isobutyl methacrylate 97% | 97-86-9 | 105 | 3 | ASTM F739 | NT | NA |
| Methanol 85% | 67-56-1 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Methanol 99% | 67-56-1 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Methyl acetate 99% | 79-20-9 | 273 | 4 | ASTM F739 | NT | NA |
| Methyl Ethyl Ketone (2-Butanone) 99% | 78-93-3 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Methyl methacrylate 95% | 80-62-6 | NT | NT | | 4 | NA |
| Methyl methacrylate 99% | 80-62-6 | 89 | 3 | EN 374-3:2003 | 4 | ++ |
| n-butyl methacrylate 99% | 97-88-1 | 90 | 3 | ASTM F739 | NT | NA |
| n-Heptane 99% | 142-82-5 | 15 | 1 | EN 374-3:2003 | 1 | - |
| N-N dimethyl acetamide 30% | 127-19-5 | 480 | 6 | ASTM F739 | NT | NA |
| N-N dimethyl acetamide 99% | 127-19-5 | 480 | 6 | ASTM F739 | NT | NA |
| Naphtha, Hydrotreated Heavy mixture | 64742-48-9 | 45 | 2 | EN 374-3:2003 | 2 | = |
| Nitric acid 10% | 7697-37-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Nitric acid 20% | 7697-37-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Nitric acid 40% | 7697-37-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Nitric acid 50% | 7697-37-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Nitric acid 68% | 7697-37-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Phosphoric acid 75% | 7664-38-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Phosphoric acid 85% | 7664-38-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Sodium hydroxide 20% | 1310-73-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Sodium hydroxide 40% | 1310-73-2 | 480 | 6 | EN 374-3:2003 | 4 | ++ |
| Sodium hydroxide 50% | 1310-73-2 | NT | NT | | 4 | NA |
| Styrene 99% | 100-42-5 | 19 | 1 | EN 374-3:2003 | 2 | = |
| Sulfuric acid 10% | 7664-93-9 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Sulfuric acid 40% | 7664-93-9 | 480 | 6 | EN 374-3:2003 | NT | NA |

*not normalized result

Overall Chemical Protection Rating

Protection rating is determined by taking into account the effects of both permeation and degradation in an attempt to provide users with an overall protection guideline when using our glove products against specific chemicals.

- Used for **high chemical exposure** or chemical immersion, limited to BTT based on a working day.
- Used for **repeated chemical contact**, limited to total chemical exposure i.e. : accumulative BTT based on a working day.
- **Splash protection only**, on chemical exposure the gloves should be discarded and new gloves worn as soon as possible.
- **Not recommended**, these gloves are deemed unsuitable for work with this chemical.
- NT : Not tested
- NA : Not applicable because not fully tested (only degradation OR permeation results)

The chemical test data and overall chemical protection rating should not be used as the absolute basis for glove selection. Actual in-use conditions may vary glove performance from the controlled conditions of laboratory tests. Factors other than chemical contact time, such as concentration and temperature, glove thickness and glove reuse, may also affect performance. Other glove requirements, such as length, dexterity, cut, abrasion, puncture and snag resistance, or glove grip also need to be considered in making your final selection.

Butoflex 650

| Chemical Product | CAS # | BTT (minutes) | Permeation level | Standard | Degradatio level | Rating |
|----------------------|-----------|---------------|------------------|---------------|------------------|--------|
| Sulfuric acid 50% | 7664-93-9 | 480 | 6 | EN 374-3:2003 | NT | NA |
| Sulfuric acid 96% | 7664-93-9 | 480 | 6 | EN 374-3:2003 | 3 | ++ |
| Tetrahydrofurane 99% | 109-99-9 | 13 | 1 | EN 374-3:2003 | 1 | - |
| Toluene 99% | 108-88-3 | 8 | 0 | EN 374-3:2003 | 1 | - |
| Vinyl acetate 99% | 108-05-4 | 212 | 4 | ASTM F739 | NT | NA |
| Xylene 99% | 1330-20-7 | 10 | 0 | EN 374-3:2003 | 1 | - |

*not normalized result

Overall Chemical Protection Rating

Protection rating is determined by taking into account the effects of both permeation and degradation in an attempt to provide users with an overall protection guideline when using our glove products against specific chemicals.

- Used for **high chemical exposure** or chemical immersion, limited to BTT based on a working day.
- Used for **repeated chemical contact**, limited to total chemical exposure i.e. : accumulative BTT based on a working day.
- **Splash protection only**, on chemical exposure the gloves should be discarded and new gloves worn as soon as possible.
- **Not recommended**, these gloves are deemed unsuitable for work with this chemical.

NT : Not tested

NA : Not applicable because not fully tested (only degradation OR permeation results)

The chemical test data and overall chemical protection rating should not be used as the absolute basis for glove selection. Actual in-use conditions may vary glove performance from the controlled conditions of laboratory tests. Factors other than chemical contact time, such as concentration and temperature, glove thickness and glove reuse, may also affect performance. Other glove requirements, such as length, dexterity, cut, abrasion, puncture and snag resistance, or glove grip also need to be considered in making your final selection.