

# Butoflex 651

## DESCRIPTION AND GENERAL PROPERTIES

- Material Butyl
- Length (inches) 14
- Thickness (inches) 0.020 (20 mil)
- Wrist Rolled cuff
- Colour/Color Black
- Interior finish Smooth
- Exterior finish Embossed texture
- Size / EAN 7 8 9 10
- Packaging 1 pair/bag - 6 pairs/carton



## PERFORMANCE RESULTS

Certification category 3

CE 0334




ABCIKL

0111

### Legends



**MECHANICAL HAZARDS EN 388**



**LOW CHEMICAL PROTECTION EN 374**




**MICRO-ORGANISMS EN 374**



**RADIOACTIVE CONTAMINATION EN 421**



**HEAT AND FIRE EN 407**




**SPECIFIC CHEMICAL PROTECTION EN 374**

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



**COLD HAZARDS EN 511**



For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

**MAPA**<sup>®</sup>  
PROFESSIONAL  
[www.mapa-pro.com](http://www.mapa-pro.com)

## DESCRIPTION AND GENERAL PROPERTIES

- Ultimate specific chemical resistance, for very corrosive acids, ketones, esters and amine derivatives
- Unrivalled flexibility and dexterity

## MAIN FIELDS OF USE

## INSTRUCTIONS FOR USE

### Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the "CE"-type tests.
- Persons sensitised to thiurames and thiazoles should not use these gloves.
- Put the gloves on dry, clean hands.
- Do not use the gloves in contact with a chemical for a duration in excess of the measured breakthrough time. Refer to the website [www.mapa-pro.com](http://www.mapa-pro.com) or contact the Technical Customer Service - MAPA PROFESSIONNEL ([stc.mapaspontex@mapaspontex.fr](mailto:stc.mapaspontex@mapaspontex.fr)) in order to know this breakthrough time. Use 2 pairs alternatively when in long duration contact with a solvent.
- Turn the cuff end down in order to prevent a hazardous chemical from dripping onto the arm.
- Inspect the gloves for cracks or snags before reusing them.

### Storage conditions

Store the gloves in their original packaging protected from humidity, heat, at mini 5°C (41°F).

### Laundering conditions

Before taking off the gloves, clean them as appropriate :

- in use with paints, pigments and inks : wipe with a clean cloth dampened with a suitable solvent, and rub over with a dry cloth
- in use with a solvent (diluent, etc...) : rub over with a dry cloth
- in use with acids and alkalies : thoroughly rinse the gloves under running water, and rub over with a dry cloth

Caution : improper use of the gloves or submitting them to any cleaning or laundering process which is not specifically recommended can alter their performance levels.

### Drying conditions

Ensure the inside of the gloves is dry before reusing them.

### Food contact US

FDA 21CFR 177.2600

## LEGISLATION

This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council. This product does not contain any substances of very high concern according to the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate  
0075/014/162/06/07/0232 EXT 01/08/07
- Issued by the notified body nr  
0075  
C.T.C -4 rue H. FRANKEL - F-69367 LYON CEDEX 07
- Quality assurance certificat  
0334 Asqual 14 rue des Reculettes -F-75013 PARIS