

Krynit Grip and Proof 581

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile GRIP&PROOF coating
- **Length (inches)** 9
- **Thickness (inches)** Heavy Wt.
- **Wrist** Knitted wrist
- **Colour/Color** Black
- **Interior finish** Seamless textile support from HDPE fibres
- **Exterior finish** Non-slip grip
- **Size / EAN** 7 8 9 10 11
- **Packaging** 1 pair/bag - 12 pairs/bag - 48 pairs/carton



PERFORMANCE RESULTS

Certification category



CUT



4543

ISO 13997 defines the weight on the blade required to cut in a single movement.


Data was obtained according to ISO 13997, from the average of several measurements. As Individual specimens will obviously have greater or lesser cut resistance than the average, so this result can provide only a general indication of the cut resistance of any protective material.

Legends



MECHANICAL HAZARDS EN 388

PERFORMANCE LEVELS



LOW CHEMICAL PROTECTION EN 374



MICRO-ORGANISMS EN 374



RADIOACTIVE CONTAMINATION EN 421




SPECIFIC CHEMICAL PROTECTION EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofuran
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%




COLD HAZARDS EN 511

PERFORMANCE LEVELS



HEAT AND FIRE EN 407

PERFORMANCE LEVELS



For more details: www.mapa-pro.com

MAPA[®]
PROFESSIONNEL
www.mapa-pro.com

DESCRIPTION AND GENERAL PROPERTIES

- Superior abrasion resistance, extends wear, reduces replacement costs
- Blue liner provides visual indicator of cut performance level
- Performance of the glove guaranteed after 5 laundering cycles (using proper procedures)

MAIN FIELDS OF USE

Automotive/mechanical industry

- Metal working
- Assembly of thin metal sheets
- Metal rolling, stamping and assembly
- Handling metal parts
- Finishing sharp parts

Glass industry

- Handling glass sheets

Mechanical industry

- Handling sharp sheet metal
- Cutting and stamping metal

INSTRUCTIONS FOR USE

Instructions for use

It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the «CE»-type tests.

It is not recommended for persons sensitized to dithiocarbamates and to natural latex (knit wrist contains elastic natural rubber).

Put the gloves on dry, clean hands.

Ensure the inside of the gloves is dry before putting them on again.

Inspect the gloves for cracks or snags before reusing them.

Do not use them next to moving machinery.

Storage conditions

Store the glove in their original packaging protected from heat, light and humidity.

Laundering conditions

Performances of the gloves are guaranteed after 5 cleaning cycles under the conditions described above: Use of a household or industrial washing machine and a standard liquid detergent, synthetic program temperature 60° C and spin drying at 400 rotations per minute. Improper use of the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

Drying conditions

Tumble drying at 60°C maximum.

Put the gloves on dry, clean hands.

Ensure the inside of the gloves is dry before putting them on again.

LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).