

# EL11LT



33.5" x 28.5" x 27.25" (H x W x D)

Commercial -45° C capable chest freezer with digital thermostat and 4.8 cu.ft. capacity

### Highlights:

Capable of -45° C operation for safe storage of vaccines and other temperature sensitive materials

UL-S listed to NSF standards for commercial use

Digital thermostat with external controls allows easy and precise temperature monitoring

### Product Features:

Commercially approved	UL-S listed to ANSI-NSF standards for use in foodservice establishments
-45° capable	Low temperature operation is ideal for select vaccines, pharmaceuticals, and frozen goods
Extra thick insulation	4 1/2" thick walls for added efficiency and stable cooling
Factory installed lock	Keyed lock on the handle for reliable security
Counterbalanced hinges	Easy and safe loading and unloading with a lid that remains open when lifted past 45° angles
Casters	Four solid wheels included for optional mobility
Digital thermostat	Electronic controls for precise temperature management, with temperature readout and controls externally located for added convenience
Access port	Factory installed probe hole allows users to install their own monitoring equipment
Manual defrost	Static cooling for a stable interior

**EL11LT Specifications:**

Overview	
Height of Cabinet	33.5" (85 cm)
Width	28.5" (72 cm)
Depth	27.25" (69 cm)
Depth with Handle	28.75" (73 cm)
Capacity	4.8 cu.ft. (136 L)
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	UL-S
Amps	3.36
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	120.0 lbs. (54 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Reversible	No
Thermostat Type	Digital
Refrigerant Type	R404a
Refrigerant Amount	3.88 oz.
High Side PSI	349.0
Low Side PSI	174.0

